



Datasheet for part number DAW-15P-1-A191

Our Catalog Part Number: DAW-15P-1-A191			
Brand: Cannon	Product Category: D Sub	Product Line: D Sub	Series: D*W

Product Datasheet	
General	Connector with IDC technology - stranded or solid wires could be terminated
Wire Gauge Range AWG	AWG 28-30
Mating Cycles	200
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	3 A (AWG 20) - 0.8 A (AWG 30)
Contact Resistance	15 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	15 contacts size 20
Gender	Pin
Contact Type	stamped
Contact Material	copper alloy
Contact Finish	gold over nickel in contact area, balance tin
Contact Termination	IDC
Mounting Methode	.120" (3,05mm) Through Hole