

MICRO SWITCHA DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH-BASIC(M) ISE3-3
ISSUE 4

ISE3-3

PAGE 1 OF 1

MDRAWING
NUMBER

ISSUE

88

9

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK

CHECK

CHECK

DRAWN


R G C

REVISIONS

A	CO18449
R G C	2 MARCH 82
B	CO-34213
J A L	24 SEPT 74
C	CO 51463-D
W J M	16 JUL 82
D	CO57041A
C J H	21 MAR 85
E	CO94274
D L M	MAR 99

FORMTEK

FO-50378



NOTE -

- ① - MOUNTING HOLES WILL ACCEPT $.007$ MAX DIA PINS OR SCREWS ON $.375 \pm .002$ CENTERS
- ② - ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ③ - WEIGHT OF SWITCH ONLY IS $.26$ OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS 1.00 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — 5-17 OZ

RELEASE FORCE — — — 4 OZ MIN

RELEASE TRAVEL — — — .004 MIN

DIFFERENTIAL TRAVEL — — — .004 MAX

OVERTRAVEL — — — .003 MIN

ELECTRICAL DATA**CONTACT ARRANGEMENT**

S P N O

250 VAC — — — — — 5 AMP

30 VOLTS DC RATING

INDUCTIVE — — — SEA LEVEL — — — 3 AMP

50,000 FT — — — 2.5 AMP

RESISTIVE — — — SEA LEVEL — — — 5 AMP

50,000 FT — — — 5 AMP

MAXIMUM INRUSH — — — — — 24 AMP

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) $\pm .030$

TWO PLACE (.00) $\pm .015$

THREE PLACE (.000) $\pm .005$

ANGLES $\pm$

WEIGHT

③

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1SE3-3](#)