

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS					
FT		0		P	LTR	DESCRIPTION	DATE	DWN	APVD
					E	REVISED PER 0G3B-0149-02	8/23/02	SS	GS

D

D

C


C

B

B

A

A



1 2

4	5.3	6.65	7.62	9.1	19.1	4.60	38.9	8	4 mm	193837-8
[.157]	[.21]	[.262]	[.300]	[.36]	[.75]	[.181]	[1.53]			
8	5.3	13.51	14.48	17.5	33	12.37	66.8	1/0	8 mm	193837-7
[.315]	[.21]	[.532]	[.570]	[.69]	[1.30]	[.487]	[2.63]			
8	5.3	13.51	14.48	14.2	33	9.91	63.5	2	8 mm	193837-6
[.315]	[.21]	[.532]	[.570]	[.56]	[1.30]	[.390]	[2.50]			
6	5.3	9.45	10.41	11.7	19.3	7.36	43.9	4	6 mm	193837-5
[.236]	[.21]	[.372]	[.410]	[.46]	[.76]	[.290]	[1.73]			
6	5.3	9.45	10.41	9.4	19.3	5.97	41.7	6	6 mm	193837-4
[.236]	[.21]	[.372]	[.410]	[.37]	[.76]	[.235]	[1.64]			
4	5.3	6.65	7.62	9.1	19.1	4.60	38.9	8	4 mm	193837-3
[.157]	[.21]	[.262]	[.300]	[.36]	[.75]	[.181]	[1.53]			
4	5.3	6.65	7.62	9.1	19.1	3.68	38.9	10	4 mm	193837-2
[.157]	[.21]	[.262]	[.300]	[.36]	[.75]	[.145]	[1.53]			
2	5.3	4.75	5.72	9.1	16.3	2.54	35.6	12/14	2 mm	193837-1
[.079]	[.21]	[.187]	[.225]	[.36]	[.64]	[.105]	[1.40]			
ϕU	K	ϕJ	ϕH	E	D	ϕC	A	WIRE AWG	PIN SIZE	PART NO.

- NOTES:
- 1 LUBRICATED AT ASSY
 - 2 PRELIMINARY PART NO.
 - 3 PIN FINISH: .200 uIN MIN. THICK SILVER OVER .500 uIN MIN THICK NICKEL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAB 08-10-93	Tyco Electronics Corporation Harrisburg, PA 17105	
DIMENSIONS: INCHES		CHK JMT 08-10-93	NAME ASSY,PIN,2-8mm,CRIMP	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	SIZE A2	
0 PLC ± -		PRODUCT SPEC -	CAGE CODE 00779	DRAWING NO 193837
1 PLC ± -		APPLICATION SPEC -	RESTRICTED TO -	
2 PLC ± 0.40 [.015]		WEIGHT -	SCALE 4:1	
3 PLC ± 0.25 [.010]		CUSTOMER DRAWING	SHEET 1 OF 1	
4 PLC ± -			REV E	
ANGLES ± -				
FINISH - 3				
MATERIAL PIN: COPPER ALLOY RETENTION SPRING: STAINLESS STEEL				