


CONFIGURATION	PART NUMBER	LENGTH
MINI, DN, THICK, M-STR, F-STR	MN57A4AD01Mxxx	TBD

DIMENSIONS



TECHNICAL DATA

TEMPERATURE RANGE:	-20C to +105C
PROTECTION:	IP 68, NEMA 6P
VOLTAGE RATING:	600VAC/600VDC
AMPERAGE:	8A
BODY:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
CONTACT PLATING:	5 INCHES (MIN) GOLD, OVER 25 INCHES (MIN) NICKEL
CONNECTOR FACE:	PVC
COUPLER:	MACHINED ALUMINUM, ANODIZED
CABLE TYPE:	DEVICE NET, THICK, UL TYPE CL2 OR PLTC
RECEPTACLE HOUSING:	MACHINED ALUMINUM, ANODIZED

--