

Item no.: 750-627
Product description: MODULE BUS EXTENSION, END MODULE



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	15 (I/O System)
Max. no. of coupler modules	bis zu 10
Current consumption max (internal)	70 mA
Buscoupler connection	1 x RJ 45 SOCKET
Isolation	500 V system / supply
Operating temperature	0 °C ... + 55 °C
Storage temperature	-25 °C ... +85 °C
Relative air humidity	95 %
Vibration resistance	acc. IEC 60068-2-6
Shock resistance	acc. IEC 60068-2-27
Degree of protection	IP 20
Conformity marking	CE
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 14 AWG
Weight	45.5 g
Color	light gray
Height	64 mm
Height	2.52 in
Width	24 mm

Width	0.945 in
Depth	100 mm
Depth	3.937 in



Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
750-627	BSH	Bescheinigung Nr. 467			
750-627	GL	19 741 - 11 HH			
750-627	UL	E175199 Sec.1			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected