

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91928

SWITCH-BASIC

CATALOG LISTING

BZ-2RQ175-A2

BZ-2RQ175-A2

PAGE 1 OF 1

REPLACES

RELEASE NO. PR-3500


DRAWING
NUMBER

10

ISSUE

REVISIONS

A	C080986	JALA	26 JUN 95
B	C093346	DLT	10 SEP 98
C	C093921	GJW	13 JAN 99
D	CO-95731-B	CSL	29 MAR 00



6-32 UNC X .218 REF BINDING
HEAD TERMINAL SCREWS
AND CUPWASHERS (3)

NOTES

- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS
- ② APPEARS ON OPPOSITE SIDE OF SWITCH
- ③ HEX NUT (1) FURNISHED UNASSEMBLED IN BULK

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE — — — — — 9-13 OZ
RELEASE FORCE — — — — — 4 OZ MIN
DIFFERENTIAL TRAVEL — — .0004-.0020
OVERTRAVEL — — — — — .125 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

-L96- 15A-125, 250 OR 480 VAC
1/8HP-125 VAC; 1/4HP-250 VAC
1/2A-125 VDC; 1/4A-250 VDC

-L288-
-L299-
-L306-

CE Ⓢ UL Ⓢ
16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED
DIMENSIONS ARE IN INCHES

TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .094 LB

FORMTEK

DRAWN

RE R 19 SEP 73 CHECK L S D 4 OCT 73 CHECK C N T 4 OCT 73 CHECK