


# Double Ultra Bright Flexible Strips from Inspired LED



- Powered by 12V DC.
- Available in a range of color temperatures:
  - Warm White (3000K)
  - Neutral White (4650K)
  - Cool White (6500K)
- 3M adhesive backing for fast, easy installation.
- Very low profile lighting:
  - 16mm wide
  - 2.4mm high
- Cut strips to custom lengths in increments of 30mm.
  - For pricing and available pre-terminated lengths, see drop down menu on product web page.
  - Available in 12 meter reels.
- 198 LED's per meter.
  - Rows of two LEDs spaced at 10.1mm
- LED lifespan rated to 50,000 hours.
- Low energy consumption, 18 watts per meter.
- No UV radiation.
- Accord with European Union CE, RoHS directive.
- Caution: bending strips to a radius of curvature less than 15mm risks damage to internal circuit traces.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Inspired LED:](#)

[DUB-3200-TR](#) [DUB-3200-CT](#) [DUB-6500-CT](#) [DUB-6500-TR](#)