




REV.	DATE	ECR NO.	DESCRIPTION
NC	03/31/11	XXXXXX	INITIAL RELEASE



RECOMMENDED
CABLE STRIPPING DIM'S



12	CONTACT PIN	BRASS	GOLD	1
11	HEX NUT	BRASS	NICKEL	1
10	WASHER	BRASS	NICKEL	1
9	GASKET	SILICONE	RED	1
8	TOP HAT	BRASS	NICKEL	1
7	WASHER	BRASS	NICKEL	1
6	SPRING	SK5	NICKEL	1
5	RETAINER RING	BRASS	NICKEL	1
4	GASKET	RUBBER	RED	1
3	INSULATOR	DELTRIN	NATURAL	1
2	BODY	BRASS	NICKEL	1
1	SHELL	ZINC DIECAST	NICKEL	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm $\pm$ 0.20mm
8 - 30mm $\pm$ 0.40mm
30 - 120mm $\pm$ 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = $\pm$ 0.007"
.315 - 1.180 = $\pm$ 0.015"
1.180 - 4.724 = $\pm$ 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	03/31/11
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE	C:/CONNEX/112352.DWG

Amphenol Connex			
PART DESCRIPTION			
BNC CLAMP PLUG (FOR RG-58C/U, 58/U, 142A/U, 223/U)			
PART NO.			
112352			
DWG. NO.	112352.DWG	REV.	NC
SIZE	A	SCALE	NA

1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"