

CIRCULAR JUNCTION BOXES

COLOUR

WHITE	BLACK
W	B

Please suffix product code with colour choice



BS 4607 Pt5.

- Note: Maximum load is 3kg at 60°C. When used to suspend lighting units, junction boxes should be used in conjunction with a steel insert clip (ref SIC 1).

Back Outlet

Size	Ref	
◆20mm	20CJB 1	20
◆25mm	25CJB 1	20

Terminal

Size	Ref	Packed
◆20mm	20CJB 2	20
◆25mm	25CJB 2	20

Through

Size	Ref	Packed
20mm	20CJB 3	20
25mm	25CJB 3	10

Angle

Size	Ref	Packed
◆20mm	20CJB 4	20
◆25mm	25CJB 4	10

3-Way Tee

Size	Ref	Packed
◆20mm	20CJB 5	20
◆25mm	25CJB 5	10

Intersection

Size	Ref	Packed
◆20mm	20CJB 6	20
◆25mm	25CJB 6	10

Terminal and Back Outlet

Size	Ref
20mm	Order 1 x 20CJB2 & 1 x PFA20
25mm	Order 1 x 25CJB2 & 1 x PFA25

Through and Back Outlet

Size	Ref
20mm	Order 1 x 20CJB3 & 1 x PFA20
25mm	Order 1 x 25CJB3 & 1 x PFA25

Angle and Back Outlet

Size	Ref
20mm	Order 1 x 20CJB4 & 1 x PFA20
25mm	Order 1 x 25CJB4 & 1 x PFA25

Tee and Back Outlet

Size	Ref
20mm	Order 1 x 20CJB5 & 1 x PFA20
25mm	Order 1 x 25CJB5 & 1 x PFA25

Intersection and Back Outlet

Size	Ref
20mm	Order 1 x 20CJB6 & 1 x PFA20
25mm	Order 1 x 25CJB6 & 1 x PFA25

No Spout

Size	Ref	Packed
◆	CJB 12	20

Loop-in

Size	Ref	Packed
With four base knock-outs:		
20mm	20CJB 13	20
With four side knock-outs:		
20mm	20CJB 20	20

Branch 'U' 2-Way Box

Size	Ref	Packed
20mm	20CJB 17	20

Branch 'Y' 3-Way Box

Size	Ref	Packed
20mm	20CJB 18	20

CIRCULAR BOX ACCESSORIES

COLOUR

WHITE	BLACK
W	B

Please suffix product code with colour choice

Screws

Self Colour Only

	Ref	Packed
Spout Locking	AB6	100
Cheese Head	M4 x 6mm	100
(Steel)	M4 x 10mm	100
	M4 x 20mm	100

Circular Lids and Gaskets 50.8mm centres

Size	Ref	Packed
◆Standard 65mm dia.	LID 1	100
Overlapping 85mm dia.	LID 2	100
Gasket 65mm dia.	GSK 1	100

Steel Insert Clip

COLOUR N/A

Size	Ref	Packed
	SIC 1	20

Brass Earth Terminals

COLOUR N/A

Size	Ref	Packed
15 amp	TER 1	100

Extension Rings

COLOUR White

Size	Ref	Packed
12.5mm	EXR 12W	50
20mm	EXR 20W	50
25mm	EXR 25W	25
38mm	EXR 38W	20
50mm	EXR 50W	10

EARTH ELECTRODE BOXES

Black box, red on white warning cover.
Plain Outlet:



Size	Ref	Packed
	MEB 1	10
Compression gland seal:		
	MEB 1/CG	10

ADAPTABLE BOXES

COLOUR White

Size	Ref	Packed
100 x 100 x 70mm deep	AJB 101070W	5
150 x 100 x 75mm deep	AJB 151075W	1
150 x 150 x 75mm deep	AJB 151575W	1

WATERPROOF BOXES IP66

COLOUR White

Size	Ref	Packed
80 x 80 x 60mm deep	WJB 080860W	1
80 x 80 x 75mm deep	WJB 080875W	1
100 x 100 x 70mm deep	WJB 101070W	1
150 x 100 x 75mm deep	WJB 151075W	1
150 x 150 x 75mm deep	WJB 151575W	1

INSTALLATION EQUIPMENT

COLOUR N/A

Adhesive

Size	Ref	Packed
Permanent	ADH 25	250ml

Draw Tapes (Nylon)

Size	Ref	Packed
10m	MDT 10	1
20m	MDT 20	1

Bending Springs

Size	Ref		
	For heavy gauge conduit (green code)	for light gauge conduit (red code)	
20mm	SPH 20	SPL 20	1
25mm	SPH 25	SPL 25	1
32mm	SPH 32	SPH 32	1

Insulation Sleeveings

Size	Ref	Packed	
	Green/Yellow	Red	
3mm	SGY 120	SR 120	100m
4mm	SGY 130	SR 130	100m

Handiburrs

Size	Ref	Packed
M3.5	HBR 3.5	1
M4	HBR 4	1