

PART
NAME


ECONOCAB

PART
No.

EC-9902 TO EC-9906




TOP VIEW



SIDE VIEW

FRONT & REAR VIEW

SECTION 'A-A'

RUBBER FOOT
0.625 DIA. x 0.218 HIGH

BOTTOM VIEW

NOTES:

MATERIAL: BODY ASSEMBLY _____ 18 GA. STEEL
HANDLE _____ ABS PLASTIC
FOOT _____ RUBBER

FINISH: BODY ASSEMBLY _____ SAND TEXTURE
BLACK TEXTURE
HANDLE _____ BLACK
FOOT _____ BLACK

MOUNTING RAILS ARE PIERCED 0.281 DIA. HOLES
ON E.I.A. UNIVERSAL SPACING.

LOAD RATING: 500 LBS. MAX.

PART NO.	DIM. A	DIM. B
EC-9902	9.062	7.062
EC-9903	10.812	8.812
EC-9904	12.562	10.562
EC-9905	14.312	12.312
EC-9906	16.062	14.062