



1	HSG. POLYPHENYLENE SULFIDE.
2	CONTACT: PHOS BRONZE.
3	DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000050-.000100 BRIGHT TIN-LEAD ON SOLDER TINES ALL OVER .000050 NICKEL ENTIRE CONTACT.
4	"AMP", "CSA", DATE CODE, AND PART NUMBER MARKED WITH .062±.015 HIGH CHARACTERS. THE ORDER AND LOCATION IS OPTIONAL.
5	POINT OF MEASUREMENT FOR PLATING THICKNESS INSIDE BEAMS.
6	TOLERANCE NON-CUMULATIVE.
7	THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES NOT THE CONTACT LOCATIONS.
8	OBSOLETE PART NUMBER.
9	PRELIMINARY PART - NOT RELEASED FOR PRODUCTION
10	DUPLEX PLATED: .000030 GOLD ON CONTACT AREA ONLY, .000050-.000100 MATTE TIN ON SOLDER TINES ALL OVER .000050 NICKEL ENTIRE CONTACT.
11	ROHS 2002/95/EC COMPLIANT.
12	OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE	10	.500	.858	12	11	6-534972-5
OBSOLETE	10	.700	1.058	16	11	6-534972-4
OBSOLETE	10	7.900	8.258	160	11 8	6-534972-3
OBSOLETE	10	6.900	7.258	140	11 8	6-534972-2
OBSOLETE	10	6.400	6.758	130	11 8	6-534972-1
OBSOLETE	10	5.900	6.258	120	11	6-534972-0
OBSOLETE	10	5.100	5.458	104	11 8	5-534972-9
OBSOLETE	10	4.900	5.258	100	11	5-534972-8
OBSOLETE	10	4.400	4.758	90	11	5-534972-7
OBSOLETE	10	3.900	4.258	80	11	5-534972-6
OBSOLETE	10	3.400	3.758	70	11	5-534972-5
OBSOLETE	10	2.900	3.258	60	11	5-534972-4
OBSOLETE	10	2.400	2.758	50	11	5-534972-3
OBSOLETE	10	1.900	2.258	40	11	5-534972-2
OBSOLETE	10	1.400	1.758	30	11	5-534972-1
9	3	.500	.858	12		1-534972-5
12	3	.700	1.058	16		1-534972-4
12	3	7.900	8.258	160	8	1-534972-3
12	3	6.900	7.258	140	8	1-534972-2
12	3	6.400	6.758	130	8	1-534972-1
12	3	5.900	6.258	120		1-534972-0
12	3	5.100	5.458	104	8	534972-9
12	3	4.900	5.258	100		534972-8
12	3	4.400	4.758	90		534972-7
12	3	3.900	4.258	80		534972-6
12	3	3.400	3.758	70		534972-5
12	3	2.900	3.258	60		534972-4
12	3	2.400	2.758	50		534972-3
12	3	1.900	2.258	40		534972-2
12	3	1.400	1.758	30		534972-1

THIS DRAWING IS A CONTROLLED DOCUMENT.	DWN M. SMITH 6-25-87	TE Connectivity			
DIMENSIONS: INCHES	CHK D. SARVER 7-8-87	NAME			
10 PLC ± -	APVD D. SARVER 7-8-87	RECEPTACLE ASSY, VERTICAL			
1 PLC ± -	PRODUCT SPEC	MT, MOD II,.100 x .100CL			
2 PLC ± -	APPLICATION SPEC	WITH MTG EARS, SHORT-POINT			
3 PLC ± .005	WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
4 PLC ± -	FINISH	A2	00779	C=534972	-
ANGLES ± -	SEE TABLE	CUSTOMER DRAWING			
FINISH	SCALE	4:1			
1 2	SHEET	1 of 1			
	REV	P3			