





NOTE:

- 1 MATERIAL:
HOUSING: 30% GLASS FILLED PBT, THERMOPLASTIC, BLACK.
CONTACT: PHOS BRONZE
- 2 FINISH: CONTACT PLATING TIN (LEAD FREE); 60 UIN MIN. OVER 30 UIN Ni
SOLDERABILITY :95% COVERAGE MIN.;
WORKING CONDITION:230°±5°C;
3. MECHANICAL SPECS:
DURABILITY: 50 CYCLES MIN.
INSERTION FORCE:300 GRAMS MAX.
WITHDRAWAL FORCE: 20 GRAMS MIN.
CONTACT RETENTION: 500 GRAMS MIN.
ACCEPTS: 0.20–0.30 [.008–.012] LEADS
4. ELECTRICAL SPECS:
VOLTAGE RATING: 250V AC,DC
CONTACT RESISTANCE: 20 MILLOHMS MAX.
CURRENT RATING: 1 AMPERE AC,DC
INSULATION RESISTANCE: 1000 MEGOHMS MIN.
DIELECTRIC WITHSTANDING VOLTAGE: AC 1000 V MIN.
5. OPERATING TEMPERATURE: –40°C TO +105°C
- 6 TE LOGO

2	40	50.80	48.26	1-2199299-5
2	28	35.56	33.02	1-2199299-2
FINISH	POS	A±0.20	B±0.15	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN WINNG WANG 18NOV2013	TE TE Connectivity	
		CHK SIMON LI 18NOV2013		
DIMENSIONS: mm		APVD COREL WANG 18NOV2013	DIP SOCKET, .600 CENTER LINE LADDER STYLE —	
		PRODUCT SPEC	SIZE	
		—	CAGE CODE	
		APPLICATION SPEC	DRAWING NO	
		—	RESTRICTED TO	
MATERIAL		WEIGHT	A1	—
1			C=2199299	—
		CUSTOMER DRAWING	SCALE 5:1	SHEET 1 OF 1 REV A