



### FEATURES:

- Supports 18 20 & 22 AWG wires.
- This in-line 2.0 (.080) dia. pin tip plug is ideal for making patch cords and field repairs
- Parts will accept 18, 20, 22 AWG wire, crimp or solder connection.
- A snap-on two piece design allows the wire to be crimped or soldered to the pin tip plug.

### MATERIALS:

Material: Brass per QQ-B-626, Alloy 360, ½ Hard

Insulation: Flexible PVC.

Marking: "POMONA"

Finish: Nickel plated per QQ-N-290, Class 2, Sulfate process, 200/300 microinches.

### RATINGS: (Independent of Wire)

Operating Temperature: +50°C. (+122°F.) Max.

Operating Voltage: 3000 VRMS

Current: 5 Amperes

### ORDERING INFORMATION: Model 5173-\*

\*=Color, -0 Black, -2 Red

Ordering Example: 5173-2 Adapter Color is Red

Parts are packaged one to a bag, unassembled.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA