

● Part Numbering

Polymer Capacitor

(Part Number)

ECAS	D4	0D	227	M	009	K	00
①	②	③	④	⑤	⑥	⑦	⑧

①Series

Product ID							
ECAS	Polymer Al Electrolytic Capacitor						

②Dimension (LxWxT) (mm)

Code	L	W	T
D4	7.3 ±0.3	4.3 ±0.2	1.9 ±0.1
D6	7.3 ±0.3	4.3 ±0.2	2.8 ±0.3
D9	7.3 ±0.3	4.3 ±0.3	4.2 ±0.3

③Rated Voltage

Code	Rated Voltage
0D	DC 2V
0E	DC 2.5V
0G	DC 4V
0J	DC 6.3V
0K	DC 8V
1A	DC 10V
1B	DC 12.5V
1C	DC 16V

④Capacitance

Expressed by three-digit numeric code.

The unit is pico-farad (pF).

The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two numbers.

Ex.)	Code	Capacitance
	476	47μF
	107	100μF
	227	220μF
	477	470μF

⑤Capacitance Tolerance

Code	Capacitance Tolerance
M	±20%

⑥ESR

Express by three-digit alphanumerics. The unit is milli-ohm (mΩ). If there is a decimal point, it is expressed by the capital letter "R".

Ex.)	Code	ESR
	4R5	4.5mΩ
	009	9mΩ
	010	10mΩ

⑦Packaging

Code	Packaging
K	ø330mm Embossed Taping

⑧Individual Specification Code

Expressed by two figures.