







MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
1201140060	BTY801N-FBC	-

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-25°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O-RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR

DESCRIPTION EC NO: WEU2010-0451 DRWN: LSTEMMLE 2010/03/22 CHKD: NSTAUDIG APPR: FPACHER 2010/03/23	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
		 = 0  = 0		mm	INCH	DRAWN BY LSTEMMLE	DATE 2010/03/22	MICRO-CHANGE MPIS TOP MOUNT 8 PORT NPN M23 CONNECTOR			
			4 PLACES	±---	±---	CHECKED BY	DATE				
			3 PLACES	±---	±---	FP	2010/03/23	MOLEX INCORPORATED			
			2 PLACES	±---	±.01	APPROVED BY	DATE				
			1 PLACE	±0.3	±---	FPACHER	2010/03/23				
ANGULAR ± --- °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-120114-081				1 OF 1		
1	REV				SIZE A2	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					