


HTHP LDD Indust X7R HT200C, Ceramic, 200C, 0.047 uF, 10%, 100 V, X7R



General Information	
Supplier:	KEMET
Series:	HTHP LDD Indust X7R HT200C
RoHS:	No
Termination:	Lead (SnPb)
Failure Rate:	N/A
Notes:	Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk

Dimensions	
D	3.94mm MAX
L	10.16mm MAX
LL	31.75mm MIN
F	0.635mm NOM

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	1

Specifications	
Capacitance:	0.047 uF
Capacitance Tolerance:	10%
Voltage DC:	100 VDC
Dielectric Withstanding Voltage:	250 V
Temperature Range:	-55/+200C
Temperature Coefficient:	X7R
Dissipation Factor:	2.5%
Insulation Resistance:	21.3 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.