


PANDUIT PART NUMBER	WIRE RANGE	COLOR CODE	DIMENSIONS in.	
			A $\pm .03$	B
DV10-250M	12-10	YELLOW	0.98 (24.9)	.235 (5.97)



NOTES :

1. USE FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 194°F (90°C) MAX TEMP RATING OF INSULATION MATERIAL
 - C. 600V MAX VOLTAGE RATING
2. MATERIAL :
 - A. STAMPING - .032" THK COPPER, NICKEL PLATED
 - B. HOUSING - VINYL
3. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
4. INSTALLATION TOOLS : CT-100, CT-260, CT-550
5. PKG QTY. -L=50
-D=500
6. WIRE STRIP LENGTH: 9/32 $^{+1/32}_{-0}$ (7.1 $^{+0.8}_{-0}$)

A41195_05

05	11/04	KLFU		ADDED #10					 PANDUIT CORP. TINLEY PARK, ILLINOIS			
04	1/01	KMD	SKB	CAD FILE SPEC. WAS N41195AA_PCD_03	8938	JAC	CCH	2PC. VINYL INSULATED, 12-10, 250 X .032 MALE TAB				
03	10/98	JD		MATERIAL WAS TIN PLATED	07642							
02	6/95	MS	LM	UPDATED NOTES AND DIMENSIONS	03404	LA	DH					
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	BLD	DRAWN BY	CHK'D	SCALE	DRAWING NO.	
								FES		NONE	A41195	