

Straight Blade Devices
Miscellaneous and Combination Receptacles
 2 Pole, 3 Wire Grounding
15 and 20 Ampere



Miscellaneous Receptacles

Description	Catalog Numbers
Receptacle, display type, brown phenolic, with .060 in. brass plate and blank flush plug.	HBL5236
Replacement receptacle for HBL5236.	HBL5236M2
Replacement threaded plug for HBL5236.	D5590401*
Receptacle, wooden floors, brown phenolic with .060 in. brass plate, blank flush plug and box.	HBL6236
Receptacle, clock hanger, brown with stainless steel plate.	HBL5235
Four outlet cluster, brown phenolic, steel cover, swivel hook. Cord grip range .296-.562 in. (7.5-14.3) cord not supplied.	HBL9259*

Note: *Not UL Listed or CSA certified.



Special Combination Duplex Receptacles

Description	Catalog Numbers
15A, 125V	Brown RTP, 1 feed, 1 return, back/side wired
	HBL4792
	Brown RTP, 2 feeds, 1 return, side wired
	HBL4794
15A, 125V	Brown RTP, 2 feeds, 2 returns, side wired
	HBL4795
15A, 250V	Brown nylon face, 2 circuit, back and side wired
	HBL5292
	Ivory nylon face, 2 circuit, back and side wired
	HBL5292I
15A, 125V	
20A, 250V	Brown nylon face, 2 circuit, back and side wired
	HBL5492
	Ivory nylon face, 2 circuit, back and side wired
	HBL5492I
20A, 125V	
15A, 125V	Brown RTP, 2 feeds, 1 return, common ground
	HBL7371
10A, 250V	
15A, 125V	
20A, 125V	Brown nylon, side and back wired
	HBL5392
20A, 125V	

Note: This device is not listed by Underwriters Laboratories Inc. nor CSA certified.

Note: This device will only accept 20A grounding plugs.

*Note: RTP is an abbreviation for reinforced thermoplastic polyester.
 See page A-44 for accessories.*

