


TERMINAL BLOCKS

SRSL 4-T32



tightening torque/thread 1.0 Nm/M 3 Inspection Test Pattern Size A 4

Type Cat.-No. Qty.p.pck.
SRSL 4-T32 41065.2 green/yellow 100


Ratings:

Dimensions TS 32
 LxBxH (mm) 56x8x52
 Stripped Length 12 mm

Max Rated Cross Section

Single Wire (solid) 0.2-6 mm²
 Stranded Wire (flexible) 0.2-4 mm²
 Wire Size AWG 22-10

SRSL 10-T32



tightening torque/thread 2.0 Nm/M 4 Inspection Test Pattern Size A 5

Type Cat.-No. Qty.p.pck.
SRSL 10-T32 41066.2 green/yellow 80


Ratings:

Dimensions TS 32
 LxBxH (mm) 56x10x52
 Stripped Length 12 mm

Max Rated Cross Section

Single Wire (solid) 0.2-10 mm²
 Stranded Wire (flexible) 0.2-10 mm²
 Wire Size AWG 20-8

SRSL 2.5-T35



tightening torque/thread 0.7 Nm/M 2.5 Inspection Test Pattern Size A 3

Type Cat.-No. Qty.p.pck.
SRSL 2.5-T35 41056.2 green/yellow 100

Ratings:

Dimensions TS 35
 LxBxH (mm) 52x6x47
 Stripped Length 10 mm

Max Rated Cross Section

Single Wire (solid) 0.2-4 mm²
 Stranded Wire (flexible) 0.2-2.5 mm²
 Wire Size AWG 22-14

SRSL 4-T35



tightening torque/thread 1.0 Nm/M 3 Inspection Test Pattern Size A 4

Type Cat.-No. Qty.p.pck.
SRSL 4-T35 41212.2 green/yellow 100

Ratings:

Dimensions TS 35
 LxBxH (mm) 56x8x47
 Stripped Length 12 mm

Max Rated Cross Section

Single Wire (solid) 0.2-6 mm²
 Stranded Wire (flexible) 0.2-4 mm²
 Wire Size AWG 22-10