







Dimensions: mm (in.)



P.C.B. Layout



Circuit Diagram

Electrical Specifications:

- Rating: Non-switching: 100mA/50V DC
Switching: 25mA/24V DC
- Contact resistance: 100mΩ max. (initial)
- Insulation resistance: 100MΩ min.

Note:

- RoHS Compliant

Mechanical Specifications:

- Operating temperature: -20°C ~ +85°C
- Operation force: 1000gf max.

Mouser Stock No.	No. of Pos.	Dim A. mm (in.)	Dim B. mm (in.)	Actuator
106-TIR4T-EV	4	11.32 (.446)	7.62 (.30)	Recessed
106-TII8-EV	8	21.48 (.846)	17.78 (.70)	Raised
106-TII9-EV	9	24.02 (.946)	20.32 (.80)	Raised
106-TIR10T-EV	10	26.56 (1.05)	22.86 (.90)	Recessed

Dip Switches (Thru-Hole)

106-TII8-EV, 106-TII9-EV, 106-TIR4T-EV, 106-TIR10T-EV