


D-subminiature shielding gaskets

VERY CONFORMABLE TO IRREGULAR SURFACES. Eliminates any gap problem between connector and I/O surface plates. Compresses from .100" to .025" (2,5 to 0,6mm). Outside conductive surface is metalized CuNi fabric at 0.005 to 0.010Ω/in.in. surface resistivity. Five sizes up to 50-conductors.



PART No.	Conductors	A	B	C	D	E	F	G
SG140009DS	9 Pin	1.40	.98	.78	.44	.22	.70	.100
SG175015DS	15 Pin	1.75	1.31	1.11	.44	.22	.70	.100
SG228025DS	25 Pin	2.28	1.85	1.65	.44	.22	.70	.100
SG293037DS	37 Pin	2.93	2.50	2.29	.44	.22	.70	.100
SG284050DS	50 Pin	2.84	2.41	2.20	.55	.28	.80	.100