


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301230140](#)
Status: **Active**
Overview: [Aero-Motive Wire-Rope Festoon Systems](#)
Description: I-Beam Festoon Intermediate Car Round S4 Steel Wheels

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Festoons
Series	130123
Cable Height - Maximum	26.16mm (1.030")
Combined Cable Weight-Max./Car	158.76kg (350.0 lb)
Component Type	Car - Intermediate
Depth	209.55mm (8.250")
Duty	Heavy
Height	336.55mm (13.250")
Length	325.88mm (12.830")
Overview	Aero-Motive Wire-Rope Festoon Systems
Product Name	Aero-Motive
Type	I-Beam
UPC	78678862929
Physical	
Beam Size	S4 - 101.60mm
Material - Coating	Powder Coating
Material - Metal	Steel
Material - Wheel	Steel
Net Weight	464.970/g
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	112.78mm (4.440")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Round
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	S639410



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130123](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION