



Wiha SoftFinish® Handle - Ergonomic Cushion Grip


Wiha SoftFinish® Handle: Featuring advanced technology dual material molding. A remarkable improvement in handle design, comfort and performance. The SoftFinish® ergonomic shape allows maximum torque and user comfort.

Wiha exclusive "SoftFinish® Zone" features solid molded core with soft outer cushion grip. Requires less force, yet achieves 40% more torque than conventional handles

Wiha Nut Drivers are precision formed to exact tolerances for a perfect fit every time

All blades are made of Wiha's exclusive formula chrome-vanadium-molybdenum tool steel, super hardened plated for unmatched durability

Handle is molded directly onto the blade for a permanent bond. Large optimized handle diameter allows higher torque with less user hand fatigue



341 Nut Driver, With Wiha-SoftFinish® Handle Inch sizes. Blade CVM steel, hardened. Deep drawn 1" socket. Solid shafts. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	Inch	Inch	mm	mm	Inch	lbs.	pkg.
341 34	9/64	5.0	125	238	9.4	.18	10
341 35	5/32	5.0	125	238	9.4	.24	10
341 36	3/16	5.0	125	238	9.4	.25	10
341 37	7/32	5.0	125	238	9.4	.26	10
341 38	1/4	5.0	125	246	9.7	.38	10
341 39	5/16	5.0	125	246	9.7	.40	10
341 40	11/32	5.0	125	246	9.7	.40	10
341 41	3/8	5.0	125	246	9.7	.40	10
341 42	7/16	5.0	125	246	9.7	.40	10
341 43	1/2	5.0	125	246	9.7	.40	10
341 44	9/16	5.0	125	246	9.7	.40	10
341 45	5/8	5.0	125	246	9.7	.40	10



341 Nut Driver, With Wiha-SoftFinish® Handle

Blade CVM steel, hardened. Deep drawn 1" socket. Solid shafts. Wiha-SoftFinish® handle, multi-component, cushion grips.

Item No.	mm	mm	Inch	mm	Inch	lbs.	pkg.
341 20	5.0	125	5.0	238	9.4	.14	10
341 21	5.5	125	5.0	238	9.4	.14	10
341 22	6.0	125	5.0	238	9.4	.15	10
341 23	7.0	125	5.0	238	9.4	.25	10
341 24	8.0	125	5.0	238	9.4	.25	10
341 25	9.0	125	5.0	238	9.4	.26	10
341 26	10.0	125	5.0	238	9.4	.27	10
341 27	11.0	125	5.0	247	9.7	.37	10
341 28	12.0	125	5.0	247	9.7	.40	10
341 29	13.0	125	5.0	247	9.7	.40	10
341 30	14.0	125	5.0	247	9.7	.40	10
341 31	15.0	125	5.0	247	9.7	.40	10



#34193



#34195

341 93 Set 7 Pcs. Nut Driver Inch Sizes

Blade chrome-vanadium-molybdenum steel, hardened.

Deep drawn 1" socket. Wiha-SoftFinish® handle, multi-component.



Deep draw 1" section with 2" section - Main body component				Deep draw 1" section with 2" section - Main body component				Deep draw 1" section with 2" section - Main body component	
Item No.									
		Inch	Inch		Inch	Inch			lbs.
341 93	341 36	3/16	5.0	341 41	3/8	5.0	1.89		
	341 38	1/4	5.0	341 42	7/16	5.0			
	341 39	5/16	5.0	341 43	1/2	5.0			
	341 40	11/32	5.0						

341 95 Set 10 Pcs. Nut Driver Inch Sizes

Item											
No.		Inch	Inch		Inch	Inch		Inch	Inch		lbs.
341 95	341 36	3/16	5.0		341 41	3/8	5.0			3.16	
	341 37	7/32	5.0		341 42	7/16	5.0				
	341 38	1/4	5.0		341 43	1/2	5.0				
	341 39	5/16	5.0		341 44	9/16	5.0				
	341 40	11/32	5.0		341 45	5/8	5.0				



341 94 Set 7 Pcs. Nut Driver Metric Sizes

COPPER PLATE PART NUMBER MEANS SIZE						
Item						
No.	mm			mm		
341 94	341 20	5.0	125	341 24	8.0	125
	341 21	5.5	125	341 26	10.0	125
	341 22	6.0	125	341 29	13.0	125
	341 23	7.0	125			
						lbs.