

TK-type Twin Wheel Caster




Characteristic

Caster with cover, drivability, stability, and smooth turning are excellent.

Application

Lighter devices / TV tables




caster with stopper
(applicable for
both truck and bolt types)

Bolt Type Specification

Model No.	A	D	E	d	H2	K	L	W	Allowable Load (kg)	Code No.
TK30N6	29	φ30	11	M6×1.0	39	10	14	33	20	19034
TK40N8	39.5	φ42	14	M8×1.25	55	14	15	39	30	19037
TK40N8S	47			19050						
TK40N10	39.5			19038						
TK40N10S	47			19051						
TK40N2.5	39.5			19039						
TK40N2.5S	47			19052						
TK40N3	39.5			19040						
TK40N3S	47			19053						
TK50N8	51.5			φ52						21
TK50N8S	59	19055								
TK50N10	51.5	19043								
TK50N10S	59	19056								
TK50N12	51.5	19044								
TK50N12S	59	M12×1.25	19		14	19057				
TK50N2.5	51.5	19045								
TK50N2.5S	59	19058								
TK50N3	51.5	19046								
TK50N3S	59	19059								

※N shows the screw type on the model No. Caster with stopper has S at the end of the model No.

Bolt type




Truck Type Specification

Model No.	A	D	E	G	H1	L1	L2	P1	P2	W	Allowable Load (kg)	Code No.		
TK30	29	φ30	11	φ5	42.5	28	28	18	18	33	20	19031		
TK40	39.5	φ42	14		58.5	38	38	26	26	40.5	30	19032		
TK40S	47				68.5					47	40	19047		
TK50	52.5	φ52	21									19033		
TK50S	59						19048							

※Caster with stopper has S at the end of the model No.

Truck type



Model No.	Material	
	Body	Wheel
TK-Type	PA	PA