



Sample photo

Order symbol: CAB ABS 303018 T
Product nbr: 8183040
Description: Cabinet, ABS
Remarks: Latches on the long side

EAN: 6418074020178
El. number:
Finland: 3424357
Denmark: 8212020537
Italy: 7812025
Sweden: 2540037
Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height
mm:	300	300	180
inch:	11.8	11.8	7.1

Materials:

Material: ABS
Base colour: RAL 7035
Cover colour: Smoked grey
Gasket material: EPDM

Temperatures:

Short term: -40 ... 80 °C
Continuous: -40 ... 60 °C
Short term: -40 ... 175 °F
Continuous: -40 ... 140 °F

Accessories:

EKIV 33 Mounting plate
EKIV 27 DIN-35 Mounting rail
DS3527OE1 DIN-35 Mounting rail
FP A 33 Swing-out door/Front plate
MB 12225 AL Swing door set
FP 33 Front plate
FP 12-33 Front plate
FP 12x2-33 Front plate
DRF 33 DIN rail frame set

Rating:

Ingress Protection (EN 60529): IP 65
Impact Resistance (EN 62262): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:

Fimko
Europe EN 62208: 2003
Gost R

