


CONFIGURATION	PART NUMBER	LENGTH
RECEPTACLE, 4 POLE, 10 AWG, FEMALE, 1/2 -14NPT, SINGLE KEY	P29026-MXX	AS REQUESTED

DIMENSIONS



TECHNICAL DATA

APPROVALS:	UL, c(UL)
STANDARD CONFORMITY:	UL 2237
TEMPERATURE RANGE:	-20C to +90C
PROTECTION:	IP 67, NEMA 6P
VOLTAGE RATING:	600VAC/600VDC
AMPERAGE:	25A
BODY:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
CONTACT PLATING:	GOLD OVER NICKEL PLATING
CONNECTOR FACE:	PVC BLACK
WIRE TYPE:	10 AWG, 600 V, THHW
RECEPTACLE HOUSING:	MACHINED ALUMINUM, ANODIZED