


ACE-828A



Specifications

Input Type	90 ~ 130VAC, 180 ~ 260VAC Auto Range					
Output Voltage	+3.3V	+5V	+12V	-5V	-12V	+5Vsb
	8A	25A (2A min)	10A (0.1A min)	0.5A	0.5A	0.72A
Efficiency	65%					
Temperature	Operating : -20 ~ 70°C (40 ~ 70°C derating curve) Storage : -40 ~ 75°C					
MTBF(hrs)	110,000					
Output Connector	20PIN ATX x1, HDD/CDROM x5, FDD x2					

Ordering Information

Part No.	Description
ACE-828A-RS	280W AC-DC PS/2 ATX Power Supply

ACE-828M



Medical



Specifications

Input Type	90 ~ 130VAC, 180 ~ 260VAC Auto Range					
Output Voltage	+3.3V	+5V	+12V	-5V	-12V	+5Vsb
	8A	25A (2A min)	10A (0.1A min)	0.5A	0.5A	0.72A
Efficiency	65%					
Temperature	Operating : -20 ~ 70°C (40 ~ 70°C derating curve) Storage : -40 ~ 75°C					
MTBF(hrs)	170,000					
Output Connector	20PIN ATX x1, HDD/CDROM x5, FDD x2					

Ordering Information

Part No.	Description
ACE-828M-RS	280W AC-DC PS/2 ATX Power Supply, meets Medical standard

ACE-932A



Specifications

Input Type	85 ~ 130 VAC, 180 ~ 265 VAC Auto Range					
Output Voltage	+3.3 V	+5 V	+12 V	-5 V	-12 V	+5 Vsb
		33A (3 A min)	8A (0.2 A min)	0.5 A	3 A	
Efficiency	68%					
Temperature	Operating : 0°C ~ 50°C (50°C ~ 70°C derating curve) Storage : -40°C ~ 75°C					
MTBF(hrs)	120,000					
Output Connector	P8+P9 x1, Extra +5V(P10) x1, HDD/CDROM x4, FDD x2					

Ordering Information

Part No.	Description
ACE-932A-RS	300 W AC-DC PS/2 AT Power Supply

ACE-925A/AP



PFC



Specifications

Input Type	85 ~ 265VAC Full Range					
Output Voltage	+3.3 V	+5 V	+12 V	-5 V	-12 V	+5 Vsb
		22 A (1A min)	7 A (0.1A min)	0.5 A	0.7 A	
Efficiency	68%					
Temperature	0°C ~ 50°C (Operating), -40°C ~ 75°C (Storage)					
MTBF(hrs)	130,000 (ACE-925A), 140,000 (ACE-925AP)					
Output Connector	P8+P9 x1, HDD/CDROM x5, FDD x2					

Ordering Information

Part No.	Description
ACE-925A-RS	200 W AC-DC PS/2 AT Power Supply
ACE-925AP-RS	200 W AC-DC PS/2 AT Power Supply, with PFC