

Intelliprint 9035N Range

Intelligent printing



- A4 High speed Mono Laser Printer for Medium to Large workgroups
- High workload 150,000 pages per month
- Fast 400Mhz Processor for fast document processing
- Intelifilter for Forms Management
- Comprehensive paper handling
- 1200 dpi for quality business documents
- Network ready

It's Fast

400 Mhz processor speed, the fastest in its class combined with TallyGenicom's market leading Intelliprint controller technology, make the 9035 the most impressive workgroup printer available today. Enough memory as standard to handle any print job, combined with fast 9 seconds first print page print time, make the 9035 the ideal printer for heavy workload applications where short print time is critical.

Productive Power

Capable of 150,000 pages per month the 9035 is built to last and at 35 pages per minute will more than meet the demands of a busy office. To cope with all this workload the 9035 can be configured with an impressive list of paper handling features including multiple bins and duplex capability making it a true workhorse.

Intelligent Migration

Legacy Data - no problem. Intelifilter resident within the 9035 enables true migration from other technologies such as a line printer or even SIDM (Serial Impact Dot Matrix). All this without expensive server software lets TallyGenicom solve all your printing problems.

Secure Printing

Add a disc drive and secure printing is enabled, just input a PIN code in the printer and collect your output. In addition Job Accounting, a Job Library, Collation and the ability to store forms, fonts and logos etc. becomes possible with the Hard Disc option.

Available Configuration:

Intelliprint 9035NL PCL5e/6 version with no internal fonts
Intelliprint 9035N PCL5e/6 version Full Extended Fonts
Intelliprint 9035NPS with Adobe Postscript 3
Intelliprint 9035NT with additional paper tray
Intelliprint 9035ND with Duplex
Intelliprint 9035NDT with Duplex and additional tray

Print Speed	Up to 35 pages per minute letter; 34 pages per minute A4
Print Method	Intelliprint Controller
Processor	R5000 400Mhz
Resolution	1200 x 1200 dpi
Time To 1st Page	Less than 9 Seconds
Memory	64MB expandable to 256MB (2 slots); Optional 20GB (or higher) hard disk
Standard Connectivity	Parallel (Bi directional IEEE 1284), USB (v2.0), Ethernet 10/100baseT (on all models)
Optional Connectivity	1 option slot available; Auto interface switching
Standard Emulation	PCL5e/PCL6
Optional Emulation	Adobe PostScript level 3
Print Monitor	TCP/IP, EtherTalk, Rendezvous, SNMP, Printer MIB, e-mail status, printer monitoring and administration via integrated web browser and TGNAdmin.
Fonts	9035NL uses Windows fonts. Other models have resident fonts
Consumables	Replacement process/toner unit < 17,000 pages*, Fuser < 200,000 pages**, Feed Roller < 200,000 pages** Initial processor/toner unit supplied with printer < 10,000 pages* *Based on 5% coverage of A4 page, **Contained within Maintenance kit
STD Paper Handling	150 sheet Universal Cassette plus 550 sheet universal cassette
Opt'l Paper Handling	3rd universal cassette accepts 550 sheets; 4th universal cassette accepts 550 sheets
Duplexing	Optional
Paper Type	Standard paper, transparencies, labels, heavy paper stock, envelopes, bond, thick media
Paper Weight	Cassettes: 60-216gsm; MPF: 60-216 gsm; Duplex: 60-216 gsm
Paper Size	Cassettes 1 and 2 - Width 98.4 - 215.9mm, Length 148mm - 355.6mm. Legal, Letter, Executive, Statement, A4, B5, 1/3 A4, Postcard, Index card, Officio. Envelopes COM 10, Monarch, C5, DL
Paper Output	500-sheet face-down top output; Optional Cassette: 500-sheet offset catch tray
Physical Weight	20.6 Kg unpacked, 26.8 Kg packed
PhysicalSize	421.8(w) x 465.4(d) x 404.3(h) mm
Power Voltage	EMEA 200-264V, USA 98-132v
Power Frequency	50/60 Hz
Compliance	Energy Star Compliant, Less than 14 Watts in sleep mode, Standby 83 Watts. Less than 350 Watts printing (average)
Workload	Up to 150,000 pages per month. 16,000 - 28,000 pages per month typical use
Reliability MTBF	300,000 pages (Power on 8hr/day in typical duty cycle)
Reliability MTTR	30 minutes
Drivers	Windows 9.x/NT 4.0/2000/XP/ME, MAC PostScript OSX, Linux via PPD
Temperature	Operating: 10° to 32° C)
Humidity	20%-80% Non-Condensing, relative humidity
Acoustic	Printing - 53.6dBA, Stand by - 27dBA, Sleep mode - Background level
Warranty	2 years on site next business day. Installation free of charge, mainland UK & Eire
Note	Exceeding the monthly duty cycle will not void the warranty if TallyGenicom consumables and maintenance kits are used. Toner saver mode providing up to 40% savings. Drum and Fuser Yields will vary based on job run length, media type, size, weight, orientation, and usage patterns.