


## 1050A, 1051A, 1052A, 1053A and 1090A Series Non-Relampable Neon-Incandescent Indicator Lights

### Description and Features



**Mounting:** Will snap-fit into Ø.500/.505 hole in panels .020/.100 thick. Push-on speednut SN0461 also available. Mounting hole pattern on page SP2.

**Wire Leads:** No. 22 AWG (105°C) 4.40/4.80 long, stripped .430/.570

**Lens:** Nylon on model 1050A1, 1050A3, 1050A4, 1050A1, 1051A3, 1051A4, Polycarbonate on all other models.

**Bezel:** Polished stainless steel. For black finish add "X" after the series letter(s).

**Housing:** White Nylon

| Lens Color | Neon                      |                           | Incandescent       |                    |
|------------|---------------------------|---------------------------|--------------------|--------------------|
|            | Model No.<br>(105-125VAC) | Model No.<br>(208-250VAC) | Model No.<br>(12V) | Model No.<br>(28V) |
| Red        | 1050A1                    | 1051A1                    | 1090A1-12V         | 1090A1-28V         |
| Clear      | 1050A2                    | 1051A2                    | -                  | -                  |
| Amber      | 1050A3                    | 1051A3                    | 1090A3-12V         | 1090A3-28V         |
| White      | 1050A4                    | 1051A4                    | 1090A4-12V         | 1090A4-28V         |
| Green      | 1052A5*                   | 1053A5*                   | 1090A5-12V         | 1090A5-28V         |
| Blue       | 1052A6**                  | 1053A6**                  | 1090A6-12V         | 1090A6-28V         |
| Lamp used  | C2A+R resistor            | C2A+R resistor            | #2162              | #2187              |
| Lead Color | Black                     | One Black/One Red         | Yellow             | Purple             |

\* Incorporates G2B lamp and resistor.

\*\* Incorporates T2B lamp and resistor.

Underwriters Laboratories (UL) File No. E20325

Canadian Standards Association (CSA) File No. LR13346