

303-2036 to 303-2322

1.27mm (.050") Pitch Picoflex™ PF-50 Custom Cable Harness, 92315



Features and Benefits

- Cable assembly with two 90327 connectors
- Sizes 4 to 20 and 26 (see 90327)
- UL 2651, 28 AWG (7 strand) ribbon cable
- Lengths from 7 to 120cm

Reference Information

- Packaging: Bag
- Mates With:

Wire-to-Board	Picoflex PF-50 Header	Low Profile 90325
		Low Profile, Vertical, Kinked PC Tails, Polarizing Peg 90715
		Low Profile, Right Angle 90800
		Low Profile, Surface Mount Compatible, High Temperature 90779
	Picoflex Header	SMT 90814

- Designed In: Millimeters

Electrical

- Voltage: 250V
- Current: 1.2A

Mechanical

- Mating Force: 1.7N
- Unmating Force: 0.25N
- Durability: 30 cycles max.

Physical

- Housing: 6/6 nylon, UL 94V-0
- Contact: Phosphor Bronze Alloy
- Plating: 3-6μ" Tin/Lead
- Temperature: -20 to +105°C
- Insulation: Cable--Gray PVC
- Wire Range: 28 AWG

See 90327 and 6800 cable pages for more specifications



DRAWING: Top, Front, Side View

ORDERING INFORMATION AND DIMENSIONS	
Circuits	Order No.
4	92315-04XX
6	92315-06XX
8	92315-08XX
10	92315-10XX
12	92315-12XX
14	92315-14XX
16	92315-16XX
18	92315-18XX
20	92315-20XX
26	92315-26XX

Length	XX
7-99cm	07-99
100cm	01
105cm	02
110cm	03
115cm	04
120cm	05

Replace XX with length in cm (min. 7cm, max. 120cm), see table
 Example: 92315-0832 is a cable with two 90327-0308, 32cm long

[[Section Index](#) | [Fax Back](#) | [Order No. Index](#) | [Trade name Index](#)]

[[Welcome!](#) | [About Us](#) | [New](#) | [Products](#) | [Contact Us](#) | [Financial](#) | [Jobs](#) | [Feedback](#)]

Top↑ © Copyright 1999 Molex Incorporated

