

Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'GEE36FR-CY'

Your search criteria matched only one product, shown below

Protects and insulates wires and cables from chafing against sharp edges

- Flame retardant (self extinguishing) material for indoor use up to 140°F (60°C)
- Provided in .030" (0.8mm) thick material making it highly flexible
- Use on irregularly shaped and round panel holes

‡Reel packaging may contain splices.

* Order the number of reels required.

**** Flame retardant products are manufactured from a material that is rated UL94-V0.**

Part Number	GEE36FR-CY
RoHS Compliancy Status	Compliant
Part Description	Slotted Wall Flame Retardant Polyethylene Grommet Edging will not support a flame. For use on curved edges or punch outs.
Material	Flame Retardant Polyethylene
Color	Natural
Height (In.)	.12
Height (mm)	3.0
Length (ft.)	100
Length (m)	30.5
Width (In.)	.11
Width (mm)	2.7
CE Compliant	No
CE Marking	No
Flammability Rating	UL94 V-0
Ft. Per Pkg.	100
Outside Depth (In.)	.117
Outside Depth (mm)	3.0
Outside Width (In.)	.11
Outside Width (mm)	2.7
Panel Thickness Range (In.)	.026 – .036
Panel Thickness Range (mm)	0.7 – 0.9
Pricing Description	Grommet Edging, Slot 100', Flame Retardant Poly, Natural
Temperature Range	-4°F to 167°F (-20°C to 75°C)
Min. Order UOM	RL
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.