





19" chassis – *multipacPRO* ServicePLUS

Individual components 19" chassis for standardised 19" assemblies

- Please select:
 - Height and depth of basic kit (1, 2 U)
 - Top cover/base plate for horizontal boards
 - Interior mounting for connector or backplane assembly
 - Front handles
 - EMC gasketing kit
 - Telescopic slides
- In accordance with standard 60297-3-100, -101, -105

Order Information

				Basic kit	top cover/base plate	Mounting of euroboards for connector EN 60603	for insulated backplane assembly
							
				06002004	06008053	06003050	06003051
				1 x Al front panel, 3 mm; 2 x Al profile side panel; 1 x Al rear panel, incl. assembly kit	Al, 1 mm; with drill hole for horizontal assembly with euroboards	2 x front horizontal rails; 2 x rear horizontal rails Z sufficient for one 3 U board as well as one 6 U board (for 1 U: 6 HP for 2 U: 15 HP)	2 x front horizontal rails; 2 x rear horizontal rails for insulated backplane assembly, threaded inserts and insulation strips sufficient for one 3 U board as well as one 6 U board (for 1 U: 6 HP for 2 U: 15 HP)
Height U	Height mm	Width HP	Depth D mm	PU 1 kit	1 piece	PU 1 kit	PU 1 kit
1	43.7	84	220	20860-201	30860-519	20860-115	20860-116
1	43.7	84	280	20860-202	30860-520	20860-115	20860-116
1	43.7	84	340	20860-203	30860-521	20860-115	20860-116
2	88.1	84	220	20860-210	30860-519	20860-117	20860-118
2	88.1	84	280	20860-211	30860-520	20860-117	20860-118
2	88.1	84	340	20860-212	30860-521	20860-117	20860-118