



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		N2	REVISED PER ECO-11-004820	11MAR11	RK	HMR

AMP WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED	12-10 AWG SOLID OR STRANDED



- 1 STAMP AMP 12-10* APPROX AS SHOWN
- 2 WIRE INSULATION DIA: .150-.250
- 3 TONGUE MATERIAL THK: 0.99 ^{±0.05} [0.039 ^{±0.002}]
- 4 TIN PLATE PER ASTM B 545
- 5 GOLD FLASH PLATE
- 6 INSULATION COLOR, YELLOW FOR P/N'S 34855, 2-34855-1, 8-34855-2 & 8-34855-4
- 7 INSULATION COLOR, RED FOR P/N'S 34855-1 & 2-34855-7
- 8 MATERIAL: BODY - CU PER ASTM B152
SLEEVE - PVC, COLOR - SEE NOTES 6 & 7

4	4	LOOSE PC,BLS	8-34855-4
4	50	LOOSE PC,BOX	8-34855-2
5	2500	ON TAPE, REEL	2-34855-7
4	2500	ON TAPE, REEL	2-34855-1
5	-	LOOSE PIECE	34855-1
4	-	LOOSE PIECE	34855
QTY		PACKAGE TYPE	PART NO.

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 08/06/92		 TE Connectivity																
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS		PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A		DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -					CHK RE HERSEY 11/10/92												
FOR APPLICATION TOOLING INFORMATION		TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED						APVD M BARNABA 11/10/92		NAME TERMINAL, RING TONGUE, PLASTI-GRIP WIRE SIZE: 12-10 AWG -													
FOR ORDER ENTRY		1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		MATERIAL 		FINISH SEE NOTES 4 & 5		PRODUCT SPEC 108-1034		APPLICATION SPEC NOT AVAILABLE		SIZE A3		CAGE CODE 00779		DRAWING NO C-34855		RESTRICTED TO -					
										CUSTOMER DRAWING										SCALE 4:1		SHEET 1 of 1		REV N2	