


Cable Ties and Edge Clips

HellermannTyton's edge clips are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place. Edge clips are available in three configurations: a two piece clip and tie assembly, a one piece clip and tie combination and an edge clip and tape bar combination. When noted (*), cable ties are outside serrated which can reduce bundle chafing.

Two Piece Edge Clip and Cable Tie Assemblies



T50ROSEC4A - the cable bundle runs parallel with the edge.

Material Data- Cable Tie

Material	Polyamide 6.6 heat stabilized (PA66HS)
Color	Black
Operating Temperature	-40 °F to +221 °F (-40 °C to +105 °C) continuous
Flammability	UL94 V2



Material Data - Edge Clip

Material	Polyamide 6.6 impact modified, heat stabilized, UV resistant (PA66HIRHS)
Color	Black
Operating Temperature	-40 °F to +230 °F (-40 °C to +110 °C) continuous
Flammability	UL94 HB



Product Selection

Product Selection			Min. Tensile Strength	Length (L)	Max. Ø Bundle	Pkg.	
Article No.	Part No.	Type	lbs. (N)	in. (mm)	in. (mm)	Qty.	Drawing
Panel Thickness, — .039" .117" (1-3mm)							
150-76090	150-76090	T30REC4A	30 lbs (135)	5.9 " (150)	1.3" (33)	500	
156-00858	156-00858	T50SOSEC4A	50 lbs (225)	5.9" (150)	1.2" (31)	500	
156-00539	156-00539	T50REC4A	50 lbs (225)	8" (202)	1.8" (45)	500	
156-00860	156-00860	T50ROSEC4A	50 lbs (225)	7.9" (200)	1.8" (45)	500	
156-00856	156-00856	T30REC4B	50 lbs (135)	5.9" (150)	1.3" (33)	500	
156-00859	156-00859	T50SOSEC4B	50 lbs (225)	6.5" (165)	1.2" (31)	500	
156-00861	156-00861	T50ROSEC4B	50 lbs (225)	8" (202)	1.8" (45)	500	
156-00538	156-00538	T50REC4B	50 lbs (225)	7.9" (200)	1.8" (45)	500	
156-00865	156-00865	T50SOSEC5A	50 lbs (225)	5.9" (150)	1.2" (31)	500	
156-00864	156-00864	T50ROSEC5A	50 lbs (225)	7.9" (200)	1.8" (45)	500	
156-01007	156-01007	T50RDHEC5A	50 lbs (225)	8.3" (210)	1.8" (45)	500	
156-00541	156-00541	T50REC5A	50 lbs (225)	7.9" (200)	1.8" (45)	500	
156-00863	156-00863	T50SOSEC5B	50 lbs (225)	5.9" (150)	1.2" (31)	500	
156-00540	156-00540	T50REC5B	50 lbs (225)	8" (202)	1.8" (45)	500	
156-00862	156-00862	T50ROSEC5B	50 lbs (225)	7.9" (200)	1.8" (45)	500	

Installation tools - MK7, MK7HT, MK7P, MK9, MK9HT, MK9P. * outside serrated cable tie. Dimensions are approximate and subject to technical changes. Use **Part No.** for ordering and **Type** for specification purposes.