

## Colo Cabinet *CL Series*

**Note:** This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **CLC Series**. For alternative solution assistance, please contact Hammond Customer Service - [sales@hammfg.com](mailto:sales@hammfg.com) or USA (716) 630-7030, Canada and International (519) 822-2960.



### Features

- One single frame allows multiple bay configurations. Mounting space includes:
  - 1-Bay = 44U, 2-Bay = 21U, 3-Bay = 14U, 4-Bay = 10U
- Standard available configurations available in 36" and 42" depths.
- Vented shelves include rear removable panels for vertical PDU installations
- Front and Rear Perforated Doors with 65% air flow.
- Doors include 4-pin combination lock with key override.
- Vertical Cable Managers can be installed either top or bottom. Designed to accommodate sliding rail mount kit on servers.
- Cabinet top includes removable top panel and provisions for containment system and cable trough accessories.

### Specifications

- 14-gauge welded steel frame; 16-gauge doors and side panel.
- Adjustable depth EIA-Compliant Adjustable depth mounting rails.
- Available as Square Hole or Tapped (10-32) mounting rail.
- Rugged textured black powder paint
- Tested to nearly double the suggested load rating of 1,800 lbs.
- RoHS Compliant.
- Manufactured in North America.

### Additional Accessories

- Third set of rails can easily be added with either 10-32 taps or square holes.
- Security upgrade kit ensures entire cabinet is tamper-proof.
- Bay upgrade kit divides a single bay into a 2, 3 or 4 bay cabinet.
- Right-hand door hinge kit.

Part No.	Overall Dimensions			Mounting Dimensions	
	Height	Width	Depth	Width	Depth
CLF244436BK	83.00	24.00	36.00	19.00	34.13
CLF244442BK	83.00	24.00	42.00	19.00	40.13

### CL Mounting Rails

Cabinet Size	Tapped 10-32 Rails (Pair)	Square Hole Rails (Pair)
10U	CLTR10U	CLSR10U

Cabinet Size	Tapped 10-32 Rails (Pair)	Square Hole Rails (Pair)
14U	CLTR14U	CLSR14U
21U	CLTR21U	CLSR21U
44U	CLTR44U	CLSR44U

## CL Internal Kit

For use with Cabinet Frame	1 Bay (44U) Part No.	2 Bay (21U) Part No.	3 Bay (14U) Part No.	4 Bay (10U) Part No.
CLF244436BK	CL1B36KIT	CL2B36KIT	CL3B36KIT	CL4B36KIT
CLF244442BK	CL1B42KIT	CL2B42KIT	CL3B42KIT	CL4B42KIT

## CL Specific Components

For use with Cabinet Frame	Solid Bottom Panel Part No.	Solid Side Panel Part No.	Solid Top Panel Part No.	Vented Top Panel Part No.
CLF244436BK	CLB2436BK	CLSP4436BK	C2T1923SBK1	C2T1923VBK1
CLF244442BK	CLB2442BK	CLSP4442BK	C2T1923SBK1	C2T1923VBK1

## CL Specific Accessories

Part No.	Description
CLSECUPG	Security Upgrade Kit
CLRHNG	Right-hand door hinge kit.
CLTROUGH	Cable Trough with Pass Through
GKIT	Cabinet Baying/Ganging/Joining Kit

*Data subject to change without notice*