

**micro plastics,®inc.***quality plastic fasteners for over 50 years*Select Your Region: United States


TOLL FREE: 800-466-1467

[Customer Login](#)**MENU**[HOME](#)[CATALOG](#)[COMPANY
INFO](#)[TECHNICAL
DATA](#)[CAPABILITIES](#)[CONTACT US](#)[DISTRIBUTORS](#)[CUSTOM
MOLDING](#)[CUSTOMERS](#)[CATALOG : PANEL FASTENERS AND HOLE PLUGS](#) : [ITEM DETAIL](#)

View Item Detail

[Search](#)[View All](#)[Need Help?](#)

Nylon Arrow Clips



Micro Plastics' Arrow Clips are reusable, molded nylon fasteners that feature an inexpensive fast method to hand assemble metal, wood, plastic, composition, or other thin gauge materials.

The specially designed body compresses as it is forced through a prepunched hole and springs back to its original shape to lock the assembled parts securely.

The versatile clips can be disassembled and reused again and again. They provide an economical, electrical insulating, vibration, abrasion, and corrosion resistant connection.

The following are some of the more common sizes. Because of Micro Plastics' unique tooling approach, designs can be varied over a wide range. Request the size you need.

** Flat Headstyle

[Filter List](#) [Advanced Sort](#) [Display Options](#)

Item Number	Description	Package Qty	Head Dia. D	Head Height A	Length B	Clip Dia. C	Hole Size	Panel Thickness Range
27AC0001	182/192H 062/125PT 360HD ACM01	1000	0.360 (+/- 0.005)	0.060 (+/- 0.005)	0.400 (+/- .010)	0.225 (+/- 0.005)	.182 / .192	.062 / .125
27AC0002	131/135H 062/125 PT 270HD M01	1000	0.270 (+/- 0.005)	0.060 (+/- 0.005)	0.395 (+/- .010)	0.160 (+/- 0.005)	.131 / .135	.062 / .125
27AC0003	151/161 HOLE 062/125PT 280DM01	1000	0.280 (+/- 0.005)	0.040 (+/- 0.005)	0.390 (+/- .010)	0.196 (+/- 0.005)	.151 / .161	.062 / .125
27AC0004	151/161H 062/145PT 280 HD M01	1000	0.280 (+/- 0.005)	0.080 (+/- 0.005)	0.400 (+/- .010)	0.180 (+/- 0.005)	.151 / .161	.062 / .145
27AC0005	213/223 HOLE 125/187PT 370DM01	1000	0.370 (+/- 0.005)	0.060 (+/- 0.005)	0.540 (+/- .010)	0.248 (+/- 0.005)	.213 / .223	.125 / .187
27AC0006	182/192HOLE 310/330PT370D M01	1000	0.370 (+/- 0.005)	0.060 (+/- 0.005)	0.540 (+/- .010)	0.225 (+/- 0.005)	.182 / .192	.310 / .330
27AC0007	213/223 HOLE .062/.125PT 370DM01	1000	0.370 (+/- 0.005)	0.060 (+/- 0.005)	0.450 (+/- 0.010)	0.227 (+/- 0.005)	.213 / .223	.062 / .125
27AC0009	250/260H 125/187PT 484HD ACM01	500	0.484 (+/- 0.005)	0.060 (+/- 0.005)	0.575 (+/- .010)	0.290 (+/- 0.005)	.250 / .260	.125 / .187
27AC0010	062/065 HOLE 010/031PT 100DM01	2500	0.100 (+/- 0.005)	0.020 (+/- 0.005)	0.125 (+/- .010)	0.068 (+/- 0.005)	.062 / .065	.010 / .031
27AC0011	182/192H 165/185PT 380HD M01	1000	0.375 (+/- 0.005)	0.060 (+/- 0.005)	0.525 (+/- .010)	0.206 (+/- 0.005)	.182 / .192	.165 / .185
1 2 3 4								
☒ Show Dimension Tolerances								

[HOME](#) : [CATALOG](#) : [PANEL FASTENERS AND HOLE PLUGS](#) : [ITEM DETAIL](#)

