


Aluminum & Steel Utility Enclosures

(1411 & 1412 Series)



Painted



Unpainted Aluminum
(Shown with protective plastic removed & partial cover)

Key Features:

- .040" thick aluminum or 20 gauge steel.
- Four self-tapping screws included.
- Unpainted aluminum or ASA 61 grey baked powder paint (outside only).
- Unpainted aluminum version is protected through manufacturing and shipping with a plastic skin cover to ensure a high quality finish.
- Replacement screws **1421J6** (Pkg. of 6, 6-32 Philips head screws).

Part Number			 Reader File	 AutoCAD .dxf File	Units	Dimensions		
Grey Aluminum	Unpainted Aluminum	Grey Steel				Length	Width	Height
1411B	1411BU	-	 21K	 18K	inch	2.7	2.2	1.6
					mm	69	56	41
1411C	1411CU	-	 21K	 18K	inch	3.2	2.2	1.1
					mm	81	56	28
1411D	1411DU	-	 21K	 18K	inch	3.2	2.2	1.6
					mm	81	56	41
1411G	1411GU	-	 21K	 18K	inch	4.0	2.2	1.6
					mm	102	56	41
1411H	1411HU	-	 21K	 18K	inch	4.0	2.2	2.2
					mm	102	56	56
1411F	1411FU	-	 21K	 18K	inch	4.0	2.2	3.0
					mm	102	56	76
1411J	1411JU	1412J	 16K	 18K	inch	4.0	4.0	2.0
					mm	102	102	51
1411K	1411KU	-	 21K	 18K	inch	5.0	2.2	2.2
					mm	127	56	56
1411N	1411NU	-	 21K	 18K	inch	5.0	3.0	2.2
					mm	127	76	56
1411L	1411LU	-	 21K	 18K	inch	5.0	4.0	3.0
					mm	127	102	76
1411M	1411MU	-	 21K	 18K	inch	6.0	3.0	3.0
					mm	152	76	76
1411PP	1411PPU	1412PP	 16K	 18K	inch	6.0	4.0	2.0
					mm	152	76	51
1411P	1411PU	-	 21K	 18K	inch	6.0	5.0	4.0
					mm	152	127	102
1411Q	1411QU	-	 21K	 18K	inch	7.0	5.0	3.0
					mm	178	127	76
1411SS	1411SSU	1412SS	 16K	 18K	inch	8.0	4.0	2.0
					mm	203	102	51
1411S	1411SU	-	 21K	 18K	inch	8.0	4.0	3.0
					mm	203	102	76
1411RR	1411RRU	1412RR	 16K	 18K	inch	8.0	6.0	2.0
					mm	203	152	51

1411R	1411RU	-	 21K	 18K	inch	8.0	6.0	3.5
					mm	203	152	89
1411T	1411TU	-	 21K	 18K	inch	10.0	2.2	1.6
					mm	254	56	41
1411TT	1411TTU	1412TT	 16K	 18K	inch	10.0	6.0	2.0
					mm	254	152	51
1411U	1411UU	-	 21K	 18K	inch	10.0	6.0	3.5
					mm	254	152	89
1411W	1411WU	-	 21K	 18K	inch	12.0	3.0	2.2
					mm	305	76	56
1411X	1411XU	1412X	 21K	 18K	inch	12.0	7.0	4.0
					mm	305	178	102
1411V	1411VU	1412V	 16K	 18K	inch	12.0	8.0	3.0
					mm	305	203	76
1411Y	1411YU	1412Y	 16K	 18K	inch	16.0	8.0	3.0
					mm	406	203	76
1411Z	1411ZU	-	 22K	 19K	inch	17.0	5.0	4.0
					mm	432	127	102