




Number of contacts

8

5 A 50 V 0.8 kV 3

Identification	Conductor cross-section (mm²)	Part number		Drawing (dimensions in mm)															
		Male	Female																
Han® Q, Data RJ45, Crimp termination  Please order crimp contacts separately.	0.13 ... 0.52	09 12 011 3001	09 12 011 3111																
D-Sub, Standard, Crimp contact 	0.13 ... 0.33 0.25 ... 0.52	09 67 000 5576 09 67 000 8576	09 67 000 5476 09 67 000 8476	<table><tr><th>Conductor cross-section</th><th>ø</th><th>Stripping length</th></tr><tr><td>0.09-0.25 mm²</td><td>0.64 mm</td><td>4 mm</td></tr><tr><td>0.13-0.33 mm²</td><td>0.88 mm</td><td>4 mm</td></tr><tr><td>0.25-0.52 mm²</td><td>1.13 mm</td><td>4 mm</td></tr><tr><td>0.33-0.82 mm²</td><td>1.34 mm</td><td>4 mm</td></tr></table> for stranded wire according IEC 60228 Class 5	Conductor cross-section	ø	Stripping length	0.09-0.25 mm²	0.64 mm	4 mm	0.13-0.33 mm²	0.88 mm	4 mm	0.25-0.52 mm²	1.13 mm	4 mm	0.33-0.82 mm²	1.34 mm	4 mm
Conductor cross-section	ø	Stripping length																	
0.09-0.25 mm²	0.64 mm	4 mm																	
0.13-0.33 mm²	0.88 mm	4 mm																	
0.25-0.52 mm²	1.13 mm	4 mm																	
0.33-0.82 mm²	1.34 mm	4 mm																	