



## 3M™ Bumpon™ Protective Products SJ5008 Black, 3000 per case

UPC# 00021200673702 3M ID 70070182772

[Print](#) [Share](#)

3M™ Bumpon™ Protective Product SJ5008 is a self-adhesive rubber bumper designed to be used as feet, stops and spacers. The flat top shape provides increased load bearing capacity and better wear resistance. Black, 0.5 in wide x 0.120 in. high.

All 3M™ Bumpon™ Protective Products feature a plasticizer-free, urethane composition which exhibits:

- Easy application with 3M pressure sensitive adhesives.
- High skid-resistance.
- Won't scratch or stain surfaces.
- Reduces vibration and noise.
- Will not crack or harden.

**Need Help?**

**Questions?** We can help  
[Contact Us](#)

**Network Access Message: The page****Overview** **Support**

Use almost anywhere slamming, scratching, nicking, scuffing, marring, sliding, vibration, or noise could be a problem for your product.

- Feet on the bottom of small appliances, desktop or handheld electronic devices, electronic cabinetry, telephones, keyboards, foot pedals, scales, clocks, speakers, dispensers, and computers.
- Stops for cabinet doors, lids, and drawers.
- Spacers for picture frames to provide alignment; for electronics and automotive applications and aid in assembly.
- Protectors to prevent damage in shipping, and keep parts from direct contact with each other.

**Specifications**

<b>Adhesive Type</b>	Natural Rubber (R30)
<b>Application</b>	Washer and Dryer Lid and Hatch Stop
<b>Availability</b>	Stocked
<b>Backing Material</b>	Polyurethane
<b>Base Width</b>	0.500 in
<b>Base Width (metric)</b>	12.7 mm
<b>Color</b>	Black
<b>Hardness</b>	72 Shore M
<b>Height</b>	0.120 Inch
<b>Height (metric)</b>	3.1 Millimetre
<b>Height-Thickness Range</b>	0.100 - 0.199 in
<b>Height-Thickness Range (metric)</b>	3.0 - 3.9 mm
<b>Market Segment</b>	Appliances
<b>Primary Liner</b>	60# Super Calendered Kraft
<b>Product Form</b>	Molded
<b>Product Series</b>	SJ5008
<b>Shape</b>	Square-Tapered w/ Flat Top
<b>Substrate</b>	ABS, Acrylic, Glass, Metals, Polycarbonate, Polyethylene, Polypropylene, Wood
<b>Width-Diameter Range</b>	0.500 - 0.599 in
<b>Width-Diameter Range (metric)</b>	10.0 - 19.9 mm

