






LOC	Q1ST	REVISED							
J		P	LTR	DESCRIPTION		ECN	DATE	DWN	APVD
			A3	REVISED PER ECO-11-005140			02APR2011	RK	HMR
			B	REVISED ECR-15-014555			09OCT2015	AY	RK




1. 適用電線; AVSS, AVSSH- f 0.3~0.5mm²
CAVS, CAVUS 0.22~0.5mm²
CHFUS 0.5mm²
HFSS- f 0.5mm²
2. アブリケータ送りピッチ; 7.5mm
3. バラ端子型番;
PRE-TIN; I376607-1
SELECTIVE GOLD; I376607-2

1. APPLICABLE WIRE RANGE;
AVSS, AVSSH-f 0.3~0.5mm²
CAVS, CAVUS 0.22~0.5mm²
CHFUS 0.5mm²
HFSS-f 0.5mm²
2. APPLICATOR FEED; 7.5mm
3. P/N OF LOOSE PIECE;
PRE-TIN; 1376607-1
SELECTIVE GOLD; 1376607-2

SELECTIVE GOLD	1376109-2
PRE-TIN	1376109-1
FINISH	PART NO.

WIRE RANGE 扭合電線斷合機		0.22~0.56mm ²		INSULATION DIA 被覆外径		Ø0.95~1.7	
				TE Connectivity			
NAME 名称							
025 TAB CONTACT							
SIZE	CAGE CODE	DRAWING NO 番号				RESTRICTED TO	
A2	00779	C-1376109				-	
SCALE 尺度				SHEET 张数		OF	REV
10.1				1		1	B

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. KOHNO	09-JUL-04
DIMENSIONS: 単位: ㎜		CHK N. SAI	09-JUL-04
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差: ±0.3		APVD K. SHIMIZU	09-JUL-04
	0-PLC	±0.3	PRODUCT SPEC 製品規格
	1-PLC	±0.5	
	2-PLC	±0.13	APPLICATION SPEC 取付適用規格
	3-PLC	±0.013	
	4-PLC	±0.0001	
ANGLES	±3°	114-5291	
MATERIAL 材料	FINISH 仕上	WEIGHT	0.19g
COPPER ALLOY		SEE TABLE	
Customer Drawing			