


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs/100pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
PRT2EH	.50 (12.7)	2.0 (51)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	9.0 (229)	250 (1112)	EXTRA HEAVY	1.6 (722)
PRT5EH	.50 (12.7)	5.0 (127.0)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	20.1 (511)	250 (1112)	EXTRA HEAVY	3.1 (1406)
PRT6EH	.50 (12.7)	6.0 (152.4)	.075 (1.9)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	22.2 (564)	250 (1112)	EXTRA HEAVY	3.6 (1633)
PRT8EH	2.5 (63.5)	8.0 (203.2)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	28.3 (719)	250 (1112)	EXTRA HEAVY	4.9 (2233)
PRT10EH	2.5 (63.5)	10.0 (254.0)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	34.2 (869)	250 (1112)	EXTRA HEAVY	5.8 (2631)
PRT12EH	2.5 (63.5)	12.0 (304.8)	.085 (2.2)	.50 (12.7)	.66 (16.8)	.40 (10.2)	.80 (20.3)	40.1 (1019)	250 (1112)	EXTRA HEAVY	6.5 (2931)

NOTES:

*1) SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS.

						TITLE		PAN-TY® RELEASABLE LASHING TIES	
						CUSTOMER DRAWING			
						ITEM REVISION NAME		108015LA/01	
						DATASET FILE NAME		108015LA/00 SS-6507.REV09	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: [IN] mm]			
						.X : .1 (2.5) .XXX : .010 (.25) .XX : .02 (1.5) ANGLES : - - - - -			
9 11/05/13 BWG RTFI KJM CORRECTED TOLERANCES. SEE ECN FOR COMPLETE DETAILS.						SS-6507/09		MATERIAL:	
8 10/24/13 BWG RTFI KJM UPDATED TITLE BORDER AND NOTE ONE.						SS-6507/08		NYLON 6.6	
						THIRD ANGLE PROJECTION		DRAWING NUMBER:	
								SS-6507	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	SCALE
							L.VALDES	7-15-77	HVP
									NONE
									SHT 1 OF 1
									SIZE
									A

2

1

D10100DA/16