



Dimensions: (In.)

SPECIFICATIONS	
Type:	3 pin DIN
Color:	grey
Contact (A):	nickel plated steel
Contact (B):	nickel plated brass
Cap:	polyethylene
Strain relief:	PVC
Insulator:	polycarbonate
Withstand voltage:	500VAC for 1 minute
Insulation resistance:	100MΩ (min) @ 500VDC
Contact resistance:	30mΩ (max)
Degrees of arc:	180°
Weight:	7g
RoHS Compliant	

Date Last Revised: 12-9-05

17PP075-E

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300905

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[17PP075-E](#)