

ROUNDLINE PLUS STAINLESS STEEL CYLINDERS

5/16" to 3" bore

Single and double acting

Full range of bore sizes

All essential models

Optional Ecology seal



TECHNICAL DATA

Medium:

Filtered, lubricated or non-lubricated,
compressed air

Maximum Operating Pressure:

250 psig (17.2 bar)

Temperature Range*:

Standard Nitrile Seals:

-20° to 200°F (-29° to 93°C)

*With dew point of supply air less than air temperature below

35°F (2°C)

Lubrication:

All Roundline Plus cylinders are pre-lubricated during assembly with a Teflon® based grease for non-lube service and long life.

Materials

Cylinder Body:

304 Stainless Steel

Head and Cap:

Aluminum Alloy

Piston Rod:

Stainless steel in double rod cylinders, and 5/16", 7/16", and 9/16" bores. Chrome plated steel in all other bore sizes

Rod Bearing: Oil Impregnated

Sintered Bronze

Piston: Aluminum Alloy or

stainless steel

Rod & Piston Seals: Nitrile

Pivot Bracket, Rod Clevis, Foot Bracket,

Mounting Nut: Bright Zinc

Plated Carbon Steel

Accessories


Bore	Pivot Bracket		Rod Clevis		Foot Bracket		Mounting Nut	
	Single Acting	Double Acting	Single Acting	Double Acting	Single Acting	Double Acting	Single Acting	Double Acting
								
5/16	PB-0	PB-0	RC-0	RC-0	FB-0S	FB-0D	MN-0	MN-1
7/16	PB-1	PB-1	RC-1	RC-1	FB-1	FB-2	MN-1	MN-2
9/16	PB-1	PB-1	RC-1	RC-1	FB-2	FB-2	MN-2	MN-2
3/4	PB-2	PB-2	RC-2	RC-2	FB-3	FB-4	MN-3	MN-4
7/8	PB-2	PB-2	RC-2	RC-2	FB-4	FB-4	MN-4	MN-4
1-1/16	PB-2	PB-2	RC-3	RC-3	FB-4	FB-4	MN-4	MN-4
1-1/4	PB-2	PB-2	RC-4	RC-4	FB-5	FB-5	MN-5	MN-5
1-1/2	PB-3	PB-3	RC-4	RC-4	FB-5	FB-5	MN-5	MN-5
1-3/4	PB-4	PB-4	RC-5	RC-5	--	FB-5A	--	MN-5A
2	PB-4	PB-4	RC-5	RC-5	--	FB-6	--	MN-6
2-1/2	PB-4	PB-4	RC-5	RC-5	--	FB-7	--	MN-7
3	PB-5	PB-5	RC-6	RC-6	--	FB-8	--	MN-8



ROUNDLINE PLUS CYLINDERS

5/16" to 3" bore

Single acting spring return
with nose mount



Dimensions

Bore	A	C	D	E	EE	G	J	K	KK	MM	N1	RM	V	Total Length
5/16"	0.38	N/A	N/A	0.36	10-32	0.25	N/A	N/A	5-40	0.125	1/4-28	.309/.312	0.03	1.12 + [0.75 per 1/2" of stroke]
7/16"	0.50	N/A	N/A	0.50	10-32	0.31	0.38	0.19	10-32	0.187	3/8-24	.369/.373	0.05	1.31 + [0.94 per 1/2" of stroke]
9/16"	0.50	N/A	N/A	0.62	10-32	0.38	0.50	0.19	10-32	0.187	7/16-20	.434/.437	0.06	1.53 + [1.62 per 1" of stroke]
3/4"	0.50	N/A	N/A	0.81	1/8 NPT	0.44	0.62	0.19	1/4-28	0.250	1/2-20	.494/.498	0.08	1.50 + [1.69 per 1" of stroke]
7/8"	0.50	N/A	N/A	0.94	1/8 NPT	0.50	0.62	0.19	1/4-28	0.250	5/8-18	.621/.624	0.09	1.84 + [1.56 per 1" of stroke]
1-1/16"	0.50	N/A	N/A	1.12	1/8 NPT	0.50	0.88	0.19	5/16-24	0.312	5/8-18	.621/.624	0.07	1.94 + [1.56 per 1" of stroke]
1-1/4"	0.75	0.25	0.38	1.34	1/8 NPT	0.63	0.88	0.25	7/16-20	0.437	3/4-16	.746/.749	0.09	2.66 + [1.81 per 1" of stroke]
1-1/2"	0.75	0.25	0.38	1.56	1/8 NPT	0.63	0.88	0.25	7/16-20	0.437	3/4-16	.746/.749	0.09	2.44 + [1.69 per 1" of stroke]

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
   								
RP031x0.500-SAN	5/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.000-SAN	5/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.500-SAN	5/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.000-SAN	5/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.500-SAN	5/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x3.000-SAN	5/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x0.500-SAN	7/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.000-SAN	7/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.500-SAN	7/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.000-SAN	7/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.500-SAN	7/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x3.000-SAN	7/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x0.500-SAN	9/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.000-SAN	9/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.500-SAN	9/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.000-SAN	9/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.500-SAN	9/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x3.000-SAN	9/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP075x0.500-SAN	3/4	1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.000-SAN	3/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.500-SAN	3/4	1-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.000-SAN	3/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.500-SAN	3/4	2-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x3.000-SAN	3/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x1.000-SAN	7/8	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x2.000-SAN	7/8	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x3.000-SAN	7/8	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x4.000-SAN	7/8	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x1.000-SAN	1-1/16	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x2.000-SAN	1-1/16	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x3.000-SAN	1-1/16	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x4.000-SAN	1-1/16	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x1.000-SAN	1-1/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x2.000-SAN	1-1/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x3.000-SAN	1-1/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x4.000-SAN	1-1/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x1.000-SAN	1-1/2	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x2.000-SAN	1-1/2	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x3.000-SAN	1-1/2	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x4.000-SAN	1-1/2	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418

Service – Quality – Delivery

NorgrenExpress.com – 1.800.514.0129 – Help@NorgrenExpress.com




ACT-21

ROUNDLINE PLUS CYLINDERS

5/16" to 3" bore

Single acting spring return
with pivot mount



Dimensions

Bore	A	CB	C	CD	D	E1	E2	EE	FL	G	KK	L	LH	M	MM	N1	N2	V	RM	Total Length
5/16"	0.38	0.25	N/A	0.125	N/A	0.36	0.36	10-32	0.34	0.25	5-40	0.19	N/A	0.16	0.125	1/4-28	3/8-24	0.03	.245/.249	1.52 + (.75 per 1/2" of stroke)
7/16"	0.50	0.31	N/A	0.156	N/A	0.50	0.74	10-32	0.44	0.31	10-32	0.25	0.50	0.25	0.187	3/8-24	7/16-20	0.05	.369/.373	1.75 + (.94 per 1/2" of stroke)
9/16"	0.50	0.31	N/A	0.156	N/A	0.62	0.62	10-32	0.38	0.38	10-32	0.25	N/A	0.19	0.187	7/16-20	7/16-20	0.06	.434/.437	1.81 + (1.62 per 1" of stroke)
3/4"	0.50	0.38	N/A	0.250	N/A	0.81	0.86	1/8 NPT	0.62	0.44	1/4-28	0.34	0.75	0.28	0.250	1/2-20	5/8-18	0.08	.494/.498	2.28 + (1.69 per 1" of stroke)
7/8"	0.50	0.38	N/A	0.250	N/A	0.94	0.94	1/8 NPT	0.62	0.50	1/4-28	0.34	0.75	0.28	0.250	5/8-18	5/8-18	0.09	.621/.624	2.47 + (1.56 per 1" of stroke)
1-1/16"	0.50	0.38	0.12	0.250	0.25	1.12	1.12	1/8 NPT	0.62	0.50	5/16-24	0.34	0.75	0.28	0.312	5/8-18	5/8-18	0.07	.621/.624	2.66 + (1.56 per 1" of stroke)
1-1/4"	0.75	0.50	0.25	0.250	0.38	1.34	1.34	1/8 NPT	0.78	0.63	7/16-20	0.41	N/A	0.40	0.437	3/4-16	3/4-16	0.09	.746/.749	3.38 + (1.81 per 1" of stroke)
1-1/2"	0.75	0.62	0.25	0.375	0.38	1.56	1.56	1/8 NPT	0.81	0.63	7/16-20	0.50	N/A	0.38	0.437	3/4-16	3/4-16	0.09	.746/.749	3.12 + (1.69 per 1" of stroke)

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
--------------	---------------	--------	-----------	-------------	------	------------------	--------------------------	--------------------




RP031x0.500-SAP	5/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.000-SAP	5/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.500-SAP	5/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.000-SAP	5/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.500-SAP	5/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x3.000-SAP	5/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x0.500-SAP	7/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.000-SAP	7/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.500-SAP	7/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.000-SAP	7/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.500-SAP	7/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x3.000-SAP	7/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x0.500-SAP	9/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.000-SAP	9/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.500-SAP	9/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.000-SAP	9/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.500-SAP	9/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x3.000-SAP	9/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP075x0.500-SAP	3/4	1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.000-SAP	3/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.500-SAP	3/4	1-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.000-SAP	3/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.500-SAP	3/4	2-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x3.000-SAP	3/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x1.000-SAP	7/8	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x2.000-SAP	7/8	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x3.000-SAP	7/8	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x4.000-SAP	7/8	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x1.000-SAP	1-1/16	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x2.000-SAP	1-1/16	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x3.000-SAP	1-1/16	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x4.000-SAP	1-1/16	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x1.000-SAP	1-1/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x2.000-SAP	1-1/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x3.000-SAP	1-1/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x4.000-SAP	1-1/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x1.000-SAP	1-1/2	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x2.000-SAP	1-1/2	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x3.000-SAP	1-1/2	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x4.000-SAP	1-1/2	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418

ROUNDLINE PLUS CYLINDERS

5/16" to 3" bore

Double acting with nose mount



Dimensions

Bore	A	C	D	EE	E1	E2	G	J	K	KK	LB	MM	N1	RM	Y	V
5/16"	0.38	N/A	N/A	10-32	0.61	0.36	0.31	0.36	N/A	5-40	1.64	0.125	3/8-24	.371/.373	0.47	0.03
7/16"	0.50	N/A	N/A	10-32	0.74	0.50	0.38	0.38	0.19	10-32	2.12	0.187	7/16-20	.434/.437	0.72	0.05
9/16"	0.50	N/A	N/A	10-32	0.62	0.62	0.38	0.50	0.19	10-32	2.28	0.187	7/16-20	.434/.437	0.75	0.06
3/4"	0.50	N/A	N/A	1/8 NPT	0.86	0.81	0.50	0.62	0.19	1/4-28	2.97	0.250	5/8-18	.621/.624	0.97	0.09
7/8"	0.50	N/A	N/A	1/8 NPT	0.94	0.94	0.50	0.62	0.19	1/4-28	2.94	0.250	5/8-18	.621/.624	0.97	0.09
1-1/16"	0.50	N/A	N/A	1/8 NPT	1.12	1.12	0.50	0.88	0.19	5/16-24	3.12	0.312	5/8-18	.621/.624	1.06	0.09
1-1/4"	0.75	0.25	0.38	1/8 NPT	1.34	1.34	0.63	0.88	0.25	7/16-20	4.00	0.437	3/4-16	.746/.749	1.37	0.09
1-1/2"	0.75	0.25	0.38	1/8 NPT	1.56	1.56	0.63	0.88	0.25	7/16-20	3.69	0.437	3/4-16	.746/.749	1.25	0.09
1-3/4"	0.88	0.31	0.44	1/4 NPT	1.84	1.84	0.75	1.25	0.25	1/2-20	4.69	0.500	1-14	1.029/1.032	1.63	0.09
2"	0.88	0.38	0.50	1/4 NPT	2.08	2.08	0.81	1.25	0.31	1/2-20	4.69	0.625	1-1/4-12	1.372/1.375	1.46	0.12
2-1/2"	0.88	0.38	0.50	1/4 NPT	2.59	2.59	0.81	1.75	0.31	1/2-20	4.69	0.625	1-3/8-12	1.497/1.500	1.46	0.12
3"	1.25	0.38	0.63	3/8 NPT	3.12	3.12	1.00	2.00	0.31	5/8-18	5.25	0.750	1-1/2-12	1.622/1.625	1.71	0.19

Models

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
--------------	---------------	--------	-----------	-------------	------	------------------	--------------------------	--------------------



RP031x0.500-DAN	5/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.000-DAN	5/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.500-DAN	5/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.000-DAN	5/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.500-DAN	5/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x3.000-DAN	5/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x4.000-DAN	5/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x5.000-DAN	5/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x6.000-DAN	5/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x0.500-DAN	7/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.000-DAN	7/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.500-DAN	7/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.000-DAN	7/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.500-DAN	7/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x3.000-DAN	7/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x4.000-DAN	7/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x5.000-DAN	7/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x6.000-DAN	7/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x0.500-DAN	9/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.000-DAN	9/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.500-DAN	9/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.000-DAN	9/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.500-DAN	9/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x3.000-DAN	9/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x4.000-DAN	9/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x5.000-DAN	9/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x6.000-DAN	9/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410

Service – Quality – Delivery

NorgrenExpress.com – 1.800.514.0129 – Help@NorgrenExpress.com



ACT-23

ROUNDLINE PLUS CYLINDERS

5/16" to 3" bore

Double acting with nose mount (cont.)

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
				  				
RP075x0.500-DAN	3/4	1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.000-DAN	3/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.500-DAN	3/4	1-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.000-DAN	3/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.500-DAN	3/4	2-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x3.000-DAN	3/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x4.000-DAN	3/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x5.000-DAN	3/4	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x6.000-DAN	3/4	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x1.000-DAN	7/8	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x2.000-DAN	7/8	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x3.000-DAN	7/8	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x4.000-DAN	7/8	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x5.000-DAN	7/8	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x6.000-DAN	7/8	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x1.000-DAN	1-1/16	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x2.000-DAN	1-1/16	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x3.000-DAN	1-1/16	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x4.000-DAN	1-1/16	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x5.000-DAN	1-1/16	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x6.000-DAN	1-1/16	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x1.000-DAN	1-1/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x2.000-DAN	1-1/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x3.000-DAN	1-1/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x4.000-DAN	1-1/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x5.000-DAN	1-1/4	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x6.000-DAN	1-1/4	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x1.000-DAN	1-1/2	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x2.000-DAN	1-1/2	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x3.000-DAN	1-1/2	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x4.000-DAN	1-1/2	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x5.000-DAN	1-1/2	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x6.000-DAN	1-1/2	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP175x1.000-DAN	1-3/4	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x2.000-DAN	1-3/4	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x3.000-DAN	1-3/4	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x4.000-DAN	1-3/4	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x5.000-DAN	1-3/4	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x6.000-DAN	1-3/4	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200x1.000-DAN	2	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200x2.000-DAN	2	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200x3.000-DAN	2	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200x4.000-DAN	2	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200x5.000-DAN	2	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200x6.000-DAN	2	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x1.000-DAN	2-1/2	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x2.000-DAN	2-1/2	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x3.000-DAN	2-1/2	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x4.000-DAN	2-1/2	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x5.000-DAN	2-1/2	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x6.000-DAN	2-1/2	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP300x1.000-DAN	3	1	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x2.000-DAN	3	2	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x3.000-DAN	3	3	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x4.000-DAN	3	4	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x5.000-DAN	3	5	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x6.000-DAN	3	6	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638


ROUNDLINE PLUS CYLINDERS

5/16" to 3" bore

Double acting with pivot mount

ACTUATORS

1



Dimensions

Bore	A	C	CB	CD	D	E	EE	FL	G	KK	L	LB	LH	MM	N1	N2	RM	V	XD	Y
5/16"	0.38	N/A	0.25	0.125	N/A	0.61	10-32	0.34	0.31	5-40	0.19	2.19	0.39	0.125	3/8-24	3/8-24	.371/.373	0.03	2.03	0.47
7/16"	0.50	N/A	0.31	0.156	N/A	0.74	10-32	0.44	0.38	10-32	0.25	2.81	0.50	0.187	7/16-20	7/16-20	.434/.437	0.05	2.56	0.72
9/16"	0.50	N/A	0.31	0.156	N/A	0.62	10-32	0.38	0.38	10-32	0.25	2.75	0.50	0.187	7/16-20	7/16-20	.434/.437	0.06	2.56	0.75
3/4"	0.50	N/A	0.38	0.250	N/A	0.86	1/8 NPT	0.62	0.50	1/4-28	0.34	4.03	0.75	0.250	5/8-18	5/8-18	.621/.624	0.09	3.75	0.97
7/8"	0.50	N/A	0.38	0.250	N/A	0.94	1/8 NPT	0.62	0.50	1/4-28	0.34	3.84	0.75	0.250	5/8-18	5/8-18	.621/.624	0.09	3.56	0.97
1-1/16"	0.50	0.12	0.38	0.250	0.25	1.12	1/8 NPT	0.62	0.50	5/16-24	0.34	4.12	0.75	0.312	5/8-18	5/8-18	.621/.624	0.09	3.84	1.07
1-1/4"	0.75	0.25	0.50	0.250	0.38	1.34	1/8 NPT	0.78	0.63	7/16-20	0.41	5.12	0.88	0.437	3/4-16	3/4-16	.746/.749	0.09	4.72	1.37
1-1/2"	0.75	0.25	0.62	0.375	0.38	1.56	1/8 NPT	0.81	0.63	7/16-20	0.50	4.75	1.00	0.437	3/4-16	3/4-16	.746/.749	0.09	4.38	1.25
1-3/4"	0.88	0.31	0.62	0.376	0.44	1.84	1/4 NPT	1.12	0.75	1/2-20	0.50	6.25	1.00	0.500	1-14	1-14	1.029/1.032	0.09	5.75	1.63
2"	0.88	0.38	0.75	0.375	0.50	2.08	1/4 NPT	1.03	0.81	1/2-20	0.56	6.06	1.63	0.625	1-1/4-12	1-1/4-12	1.372/1.375	0.12	5.62	1.54
2-1/2"	0.88	0.38	0.75	0.375	0.50	2.59	1/4 NPT	1.03	0.81	1/2-20	0.56	6.06	1.63	0.625	1-3/8-12	1-3/8-12	1.497/1.500	0.12	5.62	1.47
3"	1.25	0.38	0.88	0.500	0.63	3.12	3/8 NPT	1.34	1.00	5/8-18	0.81	7.12	1.90	0.750	1-1/2-12	1-1/2-12	1.622/1.625	0.19	6.50	1.71

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
--------------	---------------	--------	-----------	-------------	------	------------------	--------------------------	--------------------



RP031x0.500-DAP	5/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.000-DAP	5/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.500-DAP	5/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.000-DAP	5/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.500-DAP	5/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x3.000-DAP	5/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x4.000-DAP	5/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x5.000-DAP	5/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x6.000-DAP	5/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x0.500-DAP	7/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.000-DAP	7/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.500-DAP	7/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.000-DAP	7/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.500-DAP	7/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x3.000-DAP	7/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x4.000-DAP	7/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x5.000-DAP	7/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x6.000-DAP	7/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x0.500-DAP	9/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.000-DAP	9/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.500-DAP	9/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.000-DAP	9/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.500-DAP	9/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x3.000-DAP	9/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x4.000-DAP	9/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x5.000-DAP	9/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x6.000-DAP	9/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410

Service – Quality – Delivery

NorgrenExpress.com – 1.800.514.0129 – Help@NorgrenExpress.com



ACT-25

ROUNDLINE PLUS CYLINDERS


5/16" to 3" bore

Double acting with pivot mount (cont.)

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
				  				
RP075x0.500-DAP	3/4	1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.000-DAP	3/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.500-DAP	3/4	1-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.000-DAP	3/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.500-DAP	3/4	2-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x3.000-DAP	3/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x4.000-DAP	3/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x5.000-DAP	3/4	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x6.000-DAP	3/4	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x1.000-DAP	7/8	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x2.000-DAP	7/8	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x3.000-DAP	7/8	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x4.000-DAP	7/8	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x5.000-DAP	7/8	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x6.000-DAP	7/8	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x1.000-DAP	1-1/16	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x2.000-DAP	1-1/16	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x3.000-DAP	1-1/16	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x4.000-DAP	1-1/16	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x5.000-DAP	1-1/16	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x6.000-DAP	1-1/16	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x1.000-DAP	1-1/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x2.000-DAP	1-1/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x3.000-DAP	1-1/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x4.000-DAP	1-1/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x5.000-DAP	1-1/4	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x6.000-DAP	1-1/4	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x1.000-DAP	1-1/2	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x2.000-DAP	1-1/2	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x3.000-DAP	1-1/2	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x4.000-DAP	1-1/2	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x5.000-DAP	1-1/2	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x6.000-DAP	1-1/2	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP175x1.000-DAP	1-3/4	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x2.000-DAP	1-3/4	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x3.000-DAP	1-3/4	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x4.000-DAP	1-3/4	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x5.000-DAP	1-3/4	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x6.000-DAP	1-3/4	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X1.000-DAP	2	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X2.000-DAP	2	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X3.000-DAP	2	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X4.000-DAP	2	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X5.000-DAP	2	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X6.000-DAP	2	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x1.000-DAP	2-1/2	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x2.000-DAP	2-1/2	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x3.000-DAP	2-1/2	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x4.000-DAP	2-1/2	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x5.000-DAP	2-1/2	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x6.000-DAP	2-1/2	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP300x1.000-DAP	3	1	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x2.000-DAP	3	2	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x3.000-DAP	3	3	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x4.000-DAP	3	4	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x5.000-DAP	3	5	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x6.000-DAP	3	6	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638



Dimensions

Bore	A	C	D	E	EE	G	K	KK	LB	MM	N1	RM	V	Y1	Y2
5/16"	0.38	N/A	N/A	0.61	10-32	0.31	0.35	5-40	2.19	0.125	3/8-24	.371/.373	0.03	0.47	0.50
7/16"	0.50	N/A	N/A	0.74	10-32	0.38	0.50	10-32	2.81	0.187	7/16-20	.434/.437	0.05	0.73	0.69
9/16"	0.50	N/A	N/A	0.62	10-32	0.38	0.44	10-32	2.75	0.187	7/16-20	.434/.437	0.06	0.75	0.57
3/4"	0.50	N/A	N/A	0.86	1/8 NPT	0.50	0.62	1/4-28	4.03	0.250	5/8-18	.621/.624	0.09	0.97	0.90
7/8"	0.50	N/A	N/A	0.94	1/8 NPT	0.50	0.62	1/4-28	3.84	0.250	5/8-18	.621/.624	0.09	0.97	0.90
1-1/16"	0.50	0.12	0.25	1.12	1/8 NPT	0.50	0.62	5/16-24	4.12	0.312	5/8-18	.621/.624	0.09	1.07	0.90
1-1/4"	0.75	0.25	0.38	1.34	1/8 NPT	0.63	0.81	7/16-20	5.12	0.437	3/4-16	.746/.749	0.09	1.37	1.18
1-1/2"	0.75	0.25	0.38	1.56	1/8 NPT	0.63	0.62	7/16-20	4.75	0.437	3/4-16	.746/.749	0.09	1.25	0.94
1-3/4"	0.88	0.31	0.44	1.84	1/4 NPT	0.75	1.00	1/2-20	6.25	0.500	1-14	1.029/1.032	0.09	1.63	1.62
2"	0.88	0.38	0.50	2.08	1/4 NPT	0.81	1.00	1/2-20	6.06	0.625	1-1/4-12	1.372/1.375	0.12	1.46	1.47
2-1/2"	0.88	0.38	0.50	2.59	1/4 NPT	0.81	1.00	1/2-20	6.06	0.625	1-3/8-12	1.497/1.500	0.12	1.46	1.47
3"	1.25	0.38	0.63	3.12	3/8 NPT	1.00	1.43	5/8-18	7.12	0.750	1-1/2-12	1.622/1.625	0.19	1.71	1.96

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
--------------	---------------	--------	-----------	-------------	------	------------------	--------------------------	--------------------



RP031x0.500-DAD	5/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.000-DAD	5/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x1.500-DAD	5/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.000-DAD	5/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x2.500-DAD	5/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x3.000-DAD	5/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x4.000-DAD	5/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x5.000-DAD	5/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP031x6.000-DAD	5/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x0.500-DAD	7/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.000-DAD	7/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x1.500-DAD	7/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.000-DAD	7/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x2.500-DAD	7/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x3.000-DAD	7/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x4.000-DAD	7/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x5.000-DAD	7/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP043x6.000-DAD	7/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x0.500-DAD	9/16	1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.000-DAD	9/16	1	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x1.500-DAD	9/16	1-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.000-DAD	9/16	2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x2.500-DAD	9/16	2-1/2	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x3.000-DAD	9/16	3	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x4.000-DAD	9/16	4	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x5.000-DAD	9/16	5	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410
RP056x6.000-DAD	9/16	6	10-32	10-32	1/4"	C24250410	C24470410	C2VA00410

Service – Quality – Delivery

NorgrenExpress.com – 1.800.514.0129 – Help@NorgrenExpress.com



ACT-27

ROUNDLINE PLUS CYLINDERS

5/16" to 3" bore

Double acting with Double end mount (cont.)

Models

Accessories

Model Number	Cylinder Bore	Stroke	Port Size	Thread Size	Tube	Straight Fitting	90° Swivel Elbow Fitting	Banjo Flow Control
								
RP075x0.500-DAD	3/4	1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.000-DAD	3/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x1.500-DAD	3/4	1-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.000-DAD	3/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x2.500-DAD	3/4	2-1/2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x3.000-DAD	3/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x4.000-DAD	3/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x5.000-DAD	3/4	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP075x6.000-DAD	3/4	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x1.000-DAD	7/8	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x2.000-DAD	7/8	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x3.000-DAD	7/8	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x4.000-DAD	7/8	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x5.000-DAD	7/8	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP087x6.000-DAD	7/8	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x1.000-DAD	1-1/16	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x2.000-DAD	1-1/16	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x3.000-DAD	1-1/16	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x4.000-DAD	1-1/16	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x5.000-DAD	1-1/16	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP106x6.000-DAD	1-1/16	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x1.000-DAD	1-1/4	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x2.000-DAD	1-1/4	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x3.000-DAD	1-1/4	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x4.000-DAD	1-1/4	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x5.000-DAD	1-1/4	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP125x6.000-DAD	1-1/4	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x1.000-DAD	1-1/2	1	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x2.000-DAD	1-1/2	2	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x3.000-DAD	1-1/2	3	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x4.000-DAD	1-1/2	4	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x5.000-DAD	1-1/2	5	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP150x6.000-DAD	1-1/2	6	1/8 NPT	1/8" NPT	1/4"	C24250418	C24470418	C2VA00418
RP175x1.000-DAD	1-3/4	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x2.000-DAD	1-3/4	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x3.000-DAD	1-3/4	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x4.000-DAD	1-3/4	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x5.000-DAD	1-3/4	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP175x6.000-DAD	1-3/4	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X1.000-DAD	2	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X2.000-DAD	2	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X3.000-DAD	2	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X4.000-DAD	2	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X5.000-DAD	2	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP200X6.000-DAD	2	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x1.000-DAD	2-1/2	1	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x2.000-DAD	2-1/2	2	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x3.000-DAD	2-1/2	3	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x4.000-DAD	2-1/2	4	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x5.000-DAD	2-1/2	5	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP250x6.000-DAD	2-1/2	6	1/4 NPT	1/4" NPT	3/8"	C24250628	C24470628	C2VA00628
RP300x1.000-DAD	3	1	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x2.000-DAD	3	2	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x3.000-DAD	3	3	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x4.000-DAD	3	4	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x5.000-DAD	3	5	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638
RP300x6.000-DAD	3	6	3/8 NPT	3/8" NPT	3/8"	C24250638	C24470638	C2VA00638