
Item no.: 870-917
Product description: 2-Conductor earth terminal block attention! cannot be commoned!



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	16 (RAIL MOUNTED TERMINAL BLOCK WITH CCC)
Cross section [mm²]	0.08 - 2.5 mm²
Cross section [AWG]	28 - 14 AWG
Wiring method	s + f-st
Connection method	CAGE CLAMP®COMPACT CONNECTION
Cross section [mm²]	0.08 - 4 mm²
Cross section [AWG]	28 - 12 AWG
Wiring method	f
Connection method	CAGE CLAMP®COMPACT CONNECTION
Weight	4.92 g
Color	green-yellow
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	26.5 mm
Height	1.04 in
Width	5 mm
Width	0.197 in

Depth	34.5 mm
Depth	1.36 in
Strip length from	6 mm
Strip length to	7 mm



Strip length

0.26 in

Attention!

Ground (earth) conductor terminal block cannot be commoned.

Mounting

TS 15



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
870-917	ABS	05-HG476175/3-PDA	500		2,5
870-917	CCA	NL6826	500		2,5
870-917	cURus	E45172			28-12
870-917	DNV	E-9214	500		2,5
870-917	GL	17295-00HH	500		2,5
870-917	KEMA	2143311.01	500		2,5
870-917	LR	91/20112(E6)	500		2,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected