


SOT 23 SURFACE MOUNT BI-COLOR LED LAMP



UNIT : MM[INCH]
TOLERANCE : ± 0.25[± 0.01] UNLESS OTHERWISE NOTED

Selection Guide

Part No.	Dice	Lens Type	Iv (mcd) @20mA		Viewing Angle
			Min.	Typ.	2θ 1/2
KM-23ESGW-CA	HIGH EFFICIENCY RED (GaAsP/GaP)	WHITE DIFFUSED	5	10	140°
	SUPER BRIGHT GREEN (GaP)		5	10	

APPROVED: J. Lu	CHECKED: A.Chen	DRAWN : L.N. Sheu	SCALE : 3 : 1	DATA NO. : G1517	V.1
				DATE :JAN/17/2001	