





SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3, 4-2	1-5, 6-2

(ON)=MOMENTARY

NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
- TERM. NOS. FOR REFERENCE ONLY
- ELECTRICAL LIFE: 6,000 CYCLES
- OPERATING TEMP: 0°C TO 85°C
- CONTACT RESISTANCE: 10mΩ MAX. INITIAL
- 2002/95/EC (ROHS) COMPLIANT
- CONTACT RATING:
UL APPROVED: 10R(4)A 277VAC 5E4
- PLASTIC COLOR: WHITE (BODY AND ACTUATOR)
- ▲ DENOTES CRITICAL PARAMETER



TITLE PP2-7H1-2D2

A	20670	RELEASE FOR PRODUCTION	7/11/12	rc
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE 3/4:1

DATE 7/10/2012

DR rc

DWG 34-PP27H12D2

REV A