




Rating	16A 277VAC 1HP 277VAC  1/2HP 125VAC	Mounting Hole	Circuit
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	DC 500V 100M ohm Min.		
Operation Temperature	0°C~85°C		
Switch Function	3P SPDT (ON)-OFF-(ON)		

() = Momentary Function

Waterproof: IP56



RoHS Compliant

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 11/18/08

Rev. 0

Unit: mm

Checked By: **GG**

Title:
TOGGLE SWITCH

CW P/N:
GTS447G101HR