


Single-Pole Rocker Switch

PR Series



Features

- Smallest agency approved rocker switch
- Available in a variety of colors
- Low-profile design
- Mechanical life: min. 50,000 operations

Electrical Ratings				
Switch Series	EN61058 Rating	UL1054 Rating	Electrical Life at Rated Load	
			According to VDE (Min. Operations)	According to UL (Min. Operations)
PR	3A, 250VAC, T100/55	6A, 125VAC; 3A 250VAC	10,000	6,000

Electrical Specifications		Material Specifications	
Ratings:	6A, 125VAC; 3A 250VAC (cULus) 3A, 250VAC, T100/55 (VDE)	Actuator:	PBT UL 94 V-0 rated
Dielectric Strength:	1000VAC for 1 minute	Base:	PA66 UL 94 V-0 rated
Insulation Resistance:	100M ohms min at 500VDC	Spring:	Piano Wire
Initial Contact Resistance:	20μ ohms max	Contacts:	Silver Alloy
Temperature Range:	-0°C to + 100°C (VDE) -20°C to + 65°C (UL)	Movable Arm:	Silver-Plated Copper Alloy
		Terminals:	Silver-Plated Copper Alloy



RoHS Compliant
UL File No: E23301

Specifications subject to change without notice.



