

# 3M™ Bumpon™ Protective Products — Molded Shapes

## Key Customer Markets

- ◆ Electronics
- ◆ Small Appliances
- ◆ Transportation
- ◆ Furniture/Cabinetry

3M™ Bumpon™ Protective Products are pressure sensitive adhesive-backed polyurethane products that can be used as feet, stops, spacers and protectors in many applications.

### Feet

On the bottom of small appliances, electronic equipment, phones, keyboards, speakers and desk accessories.

### Stops

For cabinetry and woodworking.

### Spacers/dampers

For automotive and board rigidity in printed circuit board assembly.

### Protectors

For stacked glass and metal sheets.

## PRODUCT INFORMATION

| Product              | Color                                  | Adhesive <sup>1</sup> | Shape           | Width<br>in. (mm) | Height<br>in. (mm) | Pad<br>Format | Hardness<br>(Shore A) | Comments                                                       |
|----------------------|----------------------------------------|-----------------------|-----------------|-------------------|--------------------|---------------|-----------------------|----------------------------------------------------------------|
| <b>TRANSPARENT</b>   |                                        |                       |                 |                   |                    |               |                       |                                                                |
| SJ5302               | Transparent                            | A-20                  | Hemisphere      | 0.312 (7.9)       | 0.085 (2.2)        | 8x18          | 75                    | Universal color matching.                                      |
| SJ5303               | Transparent                            | A-20                  | Hemisphere      | 0.44 (11.1)       | 0.20 (5.0)         | 7x8           | 75                    | Universal color matching.                                      |
| SJ5306               | Transparent, White                     | A-20                  | Hemisphere      | 0.375 (9.5)       | 0.150 (3.8)        | 8x6           | 75                    | Universal color matching.                                      |
| SJ5312               | Transparent, True White                | A-20                  | Cylindrical     | 0.50 (12.7)       | 0.14 (3.6)         | 7x8           | 75                    | Universal color matching.                                      |
| SJ5382               | Transparent                            | A-20                  | Hemisphere      | 0.250 (6.4)       | 0.075 (1.9)        | 8x18          | 75                    | Universal color matching.                                      |
| <b>QUIET CLEAR</b>   |                                        |                       |                 |                   |                    |               |                       |                                                                |
| SJ6506               | Clear                                  | R-25                  | Hemisphere      | 0.375 (9.5)       | 0.150 (3.8)        | 8x12          | 55                    | Quiet Clear for cabinets.                                      |
| SJ6512               | Clear                                  | R-25                  | Cylindrical     | 0.50 (12.7)       | 0.140 (3.5)        | 7x8           | 55                    | Quiet Clear for cabinets.                                      |
| SJ6553               | Clear                                  | R-25                  | Hexagonal Cone  | 0.433 (11.0)      | 0.120 (3.05)       | 11x12         | 55                    | Quiet Clear for cabinets.                                      |
| SJ6561               | Clear                                  | R-25                  | Hex. Hemisphere | 0.433 (11.0)      | 0.150 (3.8)        | 11x12         | 55                    | Quiet Clear for cabinets.                                      |
| <b>HEMISPHERICAL</b> |                                        |                       |                 |                   |                    |               |                       |                                                                |
| SJ5003               | White, Gray, Brown, Black, Transparent | R-30                  | Hemispherical   | 0.44 (11.2)       | 0.20 (5.1)         | 7x8           | 70                    | Good energy absorption on impact.                              |
| SJ5009               | White, Gray, Brown, Black, Transparent | R-30                  | Hemispherical   | 0.88 (22.4)       | 0.40 (10.2)        | 3x8           | 70                    | Good energy absorption on impact.                              |
| SJ5017               | White, Gray, Brown, Black, Transparent | R-30                  | Hemispherical   | 0.75 (19.1)       | 0.38 (9.7)         | 4x10          | 70                    | Good energy absorption on impact.                              |
| SJ5027               | White, Gray, Brown, Black, Transparent | R-30                  | Hemispherical   | 0.63 (16.0)       | 0.31 (7.9)         | 5x8           | 70                    | Good energy absorption on impact.                              |
| SJ5402               | True White                             | A-20                  | Hemispherical   | 0.312 (7.9)       | 0.085 (2.2)        | 8x18          | 75                    | Ideal for white cabinets.                                      |
| SJ5406               | True White                             | A-20                  | Hemispherical   | 0.375 (9.5)       | 0.15 (3.8)         | 6x8           | 75                    | Ideal for white cabinets.                                      |
| MB1104-117*          | Black                                  | R-30                  | Hemispherical   | 0.232 (5.9)       | 0.114 (2.9)        | 8x18          | 70                    | Good energy absorption on impact.                              |
| MB1104-118*          | Black                                  | R-30                  | Hemispherical   | 0.630 (16.0)      | 0.118 (3.0)        | 5x4           | 70                    | Good energy absorption on impact.                              |
| MB1104-128*          | Black                                  | R-30                  | Hemispherical   | 0.216 (5.5)       | 0.095 (2.4)        | 8x18          | 70                    | Good energy absorption on impact.                              |
| MB1202-124*          | Clear                                  | A-20                  | Hemispherical   | 0.250 (6.4)       | 0.09 (2.3)         | 8x18          | 75                    | Good energy absorption on impact.                              |
| SJ5304*              | Transparent                            | A-20                  | Hemispherical   | 0.453 (11.5)      | 0.252 (6.4)        | 5x12          | 75                    | Universal color matching.<br>Good energy absorption on impact. |
| SJ5328*              | Transparent                            | R-30                  | Hemispherical   | 0.630 (16.0)      | 0.375 (9.5)        | 5x8           | 70                    | Good energy absorption on impact.                              |
| SJ5333*              | Transparent                            | A-20                  | Hemispherical   | 0.375 (9.5)       | 0.2 (5.1)          | 6x8           | 75                    | Universal color matching.                                      |
| SJ5341*              | Transparent                            | A-20                  | Hemispherical   | 0.375 (9.5)       | 0.219 (5.6)        | 6x8           | 75                    | Universal color matching.                                      |
| SJ5370*              | Transparent                            | A-20                  | Hemispherical   | 0.312 (7.9)       | 0.05 (1.3)         | 8x18          | 75                    | Good energy absorption on impact.                              |
| SJ5393*              | Transparent                            | A-20                  | Hemispherical   | 0.380 (9.7)       | 0.115 (2.9)        | 5x4           | 75                    | Universal color matching.                                      |
| SJ5395*              | Transparent                            | A-20                  | Hemispherical   | 0.560 (14.2)      | 0.325 (8.3)        | 5x8           | 75                    | Universal color matching.                                      |
| SJ5398*              | Transparent                            | A-20                  | Hemispherical   | 1.0 (25.4)        | 0.688 (17.5)       | 3x6           | 75                    | Universal color matching.                                      |
| SJ5704*              | Black, White, Gray                     | R-30                  | Hemispherical   | 0.453 (11.5)      | 0.252 (6.4)        | 5x12          | 70                    | Good energy absorption on impact.                              |
| SJ5720*              | Black                                  | R-30                  | Hemispherical   | 0.630 (16.0)      | 0.197 (5.0)        | 5x8           | 70                    | Good energy absorption on impact.                              |
| SJ5733*              | White                                  | R-30                  | Hemispherical   | 0.375 (9.5)       | 0.20 (5.1)         | 6x8           | 70                    | Good energy absorption on impact.                              |
| SJ5747*              | White                                  | R-30                  | Hemispherical   | 0.433 (11.0)      | 0.295 (7.5)        | 7x8           | 70                    | Good energy absorption on impact.                              |
| SJ5770*              | Black                                  | R-30                  | Hemispherical   | 0.312 (7.9)       | 0.05 (1.3)         | 8x18          | 70                    | Good energy absorption on impact.                              |
| SJ5788*              | Black                                  | R-30                  | Hemispherical   | 0.647 (16.4)      | 0.207 (5.3)        | 5x8           | 70                    | Good energy absorption on impact.                              |
| SJ5792*              | Gray                                   | R-30                  | Hemispherical   | 0.315 (8.0)       | 0.145 (3.7)        | 8x18          | 70                    | Good energy absorption on impact.                              |
| SJ5798*              | Black                                  | R-30                  | Hemispherical   | 1.0 (25.4)        | 0.688 (17.5)       | 3x6           | 70                    | Good energy absorption on impact.                              |

<sup>1</sup> **A-20: Acrylic** — high strength adhesion to high energy surface. **R-25: Synthetic Rubber** — ideal for low surface energy substrates.

**R-30: Natural Rubber** — excellent adhesion to a wide variety of surfaces.

\* Made to order products. Available with 10-day lead time. Minimum order 30,000 pieces.

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.

## PRODUCT INFORMATION

| Product            | Color                        | Adhesive <sup>1</sup> | Shape       | Width<br>in. (mm) | Height<br>in. (mm) | Pad<br>Format     | Hardness<br>(Shore A) | Comments                                    |
|--------------------|------------------------------|-----------------------|-------------|-------------------|--------------------|-------------------|-----------------------|---------------------------------------------|
| <b>CYLINDRICAL</b> |                              |                       |             |                   |                    |                   |                       |                                             |
| SJ5001             | Black, Transparent           | R-30                  | Cylindrical | 0.50 (12.7)       | 0.14 (3.6)         | 5x8               | 70                    | Concave top,<br>good load bearing capacity. |
| SJ5012             | White, Gray,<br>Brown, Black | R-30                  | Cylindrical | 0.50 (12.7)       | 0.14 (3.6)         | 7x8               | 70                    | Most versatile cylindrical product.         |
| SJ5076             | Black, Transparent           | R-30                  | Cylindrical | 0.315 (8.0)       | 0.11 ( 2.8 )       | 7x8               | 70                    | Versatile cylindrical product.              |
| SJ5412             | True White                   | A-20                  | Cylindrical | 0.50 (12.7)       | 0.14 (3.6)         | 7x8               | 75                    | Ideal for white cabinets.                   |
| SJ5532             | White, Gray,<br>Brown, Black | R-30                  | Cylindrical | 1.88 (47.8)       | 0.66 (16.8)        | Separate<br>Parts | 70                    | Ideal for door stops.                       |
| SJ5744             | Black, Transparent           | R-30                  | Cylindrical | 0.75 (19.1)       | 0.16 (4.1)         | 4x10              | 70                    | Excellent load bearing capacity.            |
| MB1104-107*        | Black                        | R-30                  | Cylindrical | 0.256 (6.5)       | 0.189 (4.8)        | 8x18              | 70                    | Versatile cylindrical product.              |
| SJ5316*            | Transparent                  | A-20                  | Cylindrical | 0.97 (24.6)       | 0.318 (8.1)        | 4x7               | 75                    | Universal color matching.                   |
| SJ5329*            | Clear                        | A-20                  | Cylindrical | 0.354 (9.0)       | 0.085 (2.2)        | 7x8               | 75                    | Universal color matching.                   |
| SJ5348*            | Transparent                  | A-20                  | Cylindrical | 0.787 (20.0)      | 0.244 (6.2)        | 4x4               | 75                    | Universal color matching.                   |
| SJ5360*            | Transparent                  | A-20                  | Cylindrical | 0.875 (22.2)      | 0.09 (2.3)         | 4x6               | 75                    | Universal color matching.                   |
| SJ5372*            | Transparent                  | A-20                  | Cylindrical | 1.24 (31.5)       | 0.10 (2.5)         | 3x6               | 75                    | Universal color matching.                   |
| SJ5380*            | Transparent                  | A-20                  | Cylindrical | 0.787 (20.0)      | 0.197 (5.0)        | 4x6               | 75                    | Universal color matching.                   |
| SJ5383*            | Transparent                  | A-20                  | Cylindrical | 0.5 (12.7)        | 0.191 (4.9)        | 5x8               | 75                    | Universal color matching.                   |
| SJ5716*            | Gray                         | R-30                  | Cylindrical | 0.97 (24.6)       | 0.318 (8.1)        | 4x7               | 70                    | Versatile cylindrical product.              |
| SJ5738*            | Platinum Gray                | R-30                  | Cylindrical | 0.560 (14.2)      | 0.118 (3.0)        | 5x8               | 70                    | Versatile cylindrical product.              |
| SJ5740*            | Black                        | R-30                  | Cylindrical | 0.5 (12.7)        | 0.325 (8.3)        | 5x8               | 70                    | Versatile cylindrical product.              |
| SJ5745*            | Black, White                 | R-30                  | Cylindrical | 0.5 (12.7)        | 0.25 (6.4)         | 5x12              | 70                    | Versatile cylindrical product.              |
| SJ5752*            | Black                        | R-30                  | Cylindrical | 0.315 (8.0)       | 0.197 (5.0)        | 8x18              | 70                    | Versatile cylindrical product.              |
| SJ5756P*           | Platinum Gray                | R-30                  | Cylindrical | 0.768 (19.5)      | 0.118 (3.0)        | 4x4               | 70                    | Versatile cylindrical product.              |
| SJ5772*            | Black                        | R-30                  | Cylindrical | 1.24 (31.5)       | 0.10 (2.5)         | 3x6               | 70                    | Versatile cylindrical product.              |
| SJ5773*            | Black                        | R-30                  | Cylindrical | 0.453 (11.5)      | 0.295 (7.5)        | 7x8               | 70                    | Versatile cylindrical product.              |
| SJ5780*            | Black, Gray                  | R-30                  | Cylindrical | 0.787 (20.0)      | 0.197 (5.0)        | 4x6               | 70                    | Versatile cylindrical product.              |

<sup>1</sup> **A-20: Acrylic** — high strength adhesion to high energy surface. **R-25: Synthetic Rubber** — ideal for low surface energy substrates.

**R-30: Natural Rubber** — excellent adhesion to a wide variety of surfaces.

\*Made to order products. Available with 10-day lead time. Minimum order 30,000 pieces.

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.



**Protective Cushioners** **Fig.097**

Gourmet appliances won't mar surfaces when you select from a vast array of 3M™ Bumpon™ Products. 3M offers several self sticking pressure sensitive adhesives, which help you build in time and labor savings by eliminating the need to drill, rivet or attach push-in feet. We also offer total customization enabling you to determine the exact size, shape and color you need.



**Clear Protective Cushioners** **Fig.098**

5300 series clear Bumpon™ Products are ideal for glass and acrylic cutting boards and other colored surfaces. Because these clear bumpers are nearly invisible and resist yellowing with age, product designs remain ageless over time.



**Protective Spacers** **Fig.099**

5000 and 5300 series Bumpon™ Products are used as non-slip spacers on medical tabletops, electronic assemblies, and lids. They are also used as spacers to help protect delicate printed circuit boards from vibration and heat build-up.



**Protective Spacers** **Fig.100**

For noise and vibration control: The highly durable 5400 series true white Bumpon™ Products are ideal for stops on doors and drawers. These bumpers help absorb impact and noise and have excellent resistance to aging; they will not harden or crack over time.



**Printed Circuit Board Spacers** **Fig.101**

Maintain performance of automotive computer systems by reducing heat build-up and vibration, plus preventing board flexing.



**Rear Windshield Sound Dampers** **Fig.102**

Adhere to the frame on SUV rear windshields and eliminate squeaking at the corners.

| Product                              | Color                                  | Adhesive <sup>1</sup> | Shape                              | Width<br>in. (mm)             | Height<br>in. (mm) | Pad<br>Format | Hardness<br>(Shore A) | Comments                                                                    |
|--------------------------------------|----------------------------------------|-----------------------|------------------------------------|-------------------------------|--------------------|---------------|-----------------------|-----------------------------------------------------------------------------|
| <b>CYLINDRICAL (Continued)</b>       |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| SJ57A12*                             | Black                                  | R-30                  | Cylindrical                        | 0.312 (7.9)                   | 0.08 (2.0)         | 8x18          | 70                    | Versatile cylindrical product.                                              |
| SJ57B1*                              | Black                                  | R-30                  | Cylindrical                        | 0.5 (12.7)                    | 0.051 (1.3)        | 5x8           | 70                    | Versatile cylindrical product.                                              |
| SJ6145*                              | Black, White                           | R-25                  | Cylindrical                        | 0.5 (12.7)                    | 0.25 (6.4)         | 5x12          | 70                    | Quick stick adhesive.                                                       |
| SJ6148*                              | Black                                  | R-25                  | Cylindrical                        | 0.787 (20.0)                  | 0.244 (6.2)        | 4x4           | 70                    | Quick stick R25 adhesive.                                                   |
| SJ6160*                              | Black                                  | R-25                  | Cylindrical                        | 0.875 (22.2)                  | 0.09 (2.3)         | 4x6           | 70                    | Quick stick R25 adhesive.                                                   |
| <b>SQUARE</b>                        |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| SJ5007                               | White, Black, Transparent              | R-30                  | Tapered Square                     | 0.41 (10.4)                   | 0.10 (2.5)         | 6x9           | 70                    | Good load bearing capacity.                                                 |
| SJ5008                               | White, Gray, Brown, Black, Transparent | R-30                  | Tapered Square                     | 0.50 (12.7)                   | 0.12 (3.1)         | 8x10          | 70                    | Good load bearing capacity.                                                 |
| SJ5018                               | White, Gray, Brown, Black, Transparent | R-30                  | Tapered Square                     | 0.50 (12.7)                   | 0.23 (5.8)         | 8x10          | 70                    | Good load bearing capacity.                                                 |
| SJ5023                               | White, Gray, Brown, Black, Transparent | R-30                  | Tapered Square                     | 0.81 (20.6)                   | 0.30 (7.6)         | 4x9           | 70                    | Good load bearing capacity.                                                 |
| SJ5514                               | White, Gray, Brown, Black              | R-30                  | Tapered Square                     | 0.81 (20.6)                   | 0.52 (13.2)        | 1x4           | 70                    | Excellent load bearing capacity.                                            |
| SJ5705                               | Black                                  | R-30                  | Tapered Square                     | 1.28 (32.4)                   | 0.25 (6.4)         | 3x3           | 70                    | Excellent load bearing capacity.                                            |
| <b>HEXAGON</b>                       |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| SJ5077                               | Black, Transparent                     | R-30                  | Hex. Width Flat Top                | 0.75 (19.1)                   | 0.16 (4.1)         | 39/pad        | 70                    | Good energy absorption on impact.                                           |
| SJ5201                               | Light Brown                            | R-25                  | Hexagon Die-cut                    | 0.43 (11.0)                   | 0.125 (3.2)        | 11x12         | 25                    | Ideal for cabinets.                                                         |
| SJ5202                               | Black, Transparent                     | R-25                  | Hexagon Die-cut                    | 0.43 (11.0)                   | 0.063 (1.6)        | 11x12         | 25                    | Ideal for cabinets.                                                         |
| <b>PRINTED CIRCUIT BOARD SPACERS</b> |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| SJ67A1                               | Black                                  | R-25                  | Cylindrical                        | .312 (7.9)                    | .200 (5.1)         | 8x18          | 85                    | Provides design flexibility.                                                |
| SJ67A2                               | Black                                  | R-25                  | Hemisphere                         | .375 (9.5)                    | .235 (6.0)         | 8x12          | 85                    | Adheres to a wide variety of substrates.                                    |
| SJ67A3                               | Black                                  | R-25                  | Cylindrical                        | .375 (9.5)                    | .250 (6.35)        | 8x12          | 85                    | Highly popular and versatile shape.                                         |
| SJ67A4                               | Black                                  | R-25                  | Cylindrical                        | .375 (9.5)                    | .311 (7.9)         | 8x6           | 85                    | The taller height is ideal for proper spacing between boards.               |
| SJ67A6                               | Black                                  | R-25                  | Cylindrical                        | .312 (7.9)                    | .215 (5.5)         | 8x18          | 85                    | Helps safeguard against the possibility of short-circuiting between boards. |
| SJ67A8                               | Black                                  | R-25                  | Cylindrical                        | .375 (9.5)                    | .135 (3.4)         | 8x18          | 85                    | Ideal where less height is needed.                                          |
| SJ67A9                               | Black                                  | R-25                  | Cylindrical Cone                   | .312 (7.9)                    | .388 (9.8)         | 8x6           | 85                    | The tallest of the PCB shapes.                                              |
| SJ61A10                              | Black                                  | R-25                  | Cylindrical                        | .685 (17.4)                   | .470 (11.9)        | 4x6           | 70                    | Used to limit vibrations.                                                   |
| SJ67A11                              | Black                                  | R-25                  | Cylindrical                        | .312 (7.9)                    | .210 (5.3)         | 8x18          | 85                    | Provides design flexibility over mechanical spacers.                        |
| <b>TOP-HAT</b>                       |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| SJ6115                               | Black                                  | R-25                  | Cylindrical                        | 0.625 (15.9)                  | 0.187 (4.75)       | 5x8           | 70                    | Quick stick R25 adhesive.                                                   |
| SJ6125                               | Black                                  | R-25                  | Hemisphere                         | 0.625 (15.9)                  | 0.25 (6.35)        | 5x8           | 70                    | Quick stick R25 adhesive.                                                   |
| <b>EASY SLIDE</b>                    |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| SJ6344                               | Black                                  | R-25                  | Cylindrical                        | 0.75 (19.0)                   | 0.16 (4.0)         | 4x10          | 80                    | Use as low friction, easy slide guide.                                      |
| <b>CUSTOMIZED SHAPES*</b>            |                                        |                       |                                    |                               |                    |               |                       |                                                                             |
| MB1102-113                           | Gray                                   | A-20                  | Oval                               | 0.551 (14.0)                  | 0.079 (2.0)        | 5x4           | 75                    | Load bearing.                                                               |
| MB1104-101                           | Black                                  | R-30                  | Rectangular                        | 0.315 x 0.709<br>(8.0 x 18.0) | 0.236 (6.0)        | 5x12          | 70                    | Larger, flat surface design.                                                |
| MB1104-102                           | Black                                  | R-30                  | Oval                               | 0.298 (7.6)                   | 0.118 (3.0)        | 1x9           | 70                    | Larger, flat surface design.                                                |
| MB1104-105                           | Black                                  | R-30                  | Dog-Bone                           | 0.315 x 1.28<br>(8.0 x 32.5)  | 0.157 (4.0)        | 9x2           | 70                    | Unique foot design.                                                         |
| MB1104-106                           | Platinum Gray                          | R-30                  | Elliptical                         | .0316 (8.0)                   | 0.156 (4.0)        | 8x4           | 70                    | Popular foot design, unique shape.                                          |
| MB1104-108                           | Black                                  | R-30                  | Cylindrical with Hemispherical Top | 0.433 (11.0)                  | 0.283 (7.2)        | 7x8           | 70                    | Unique shape, energy absorption.                                            |

<sup>1</sup> **A-20: Acrylic** — high strength adhesion to high energy surface. **R-25: Synthetic Rubber** — ideal for low surface energy substrates.

**R-30: Natural Rubber** — excellent adhesion to a wide variety of surfaces.

\*Made to order products. Available with 10-day lead time. Minimum order 30,000 pieces.

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.



**Customized Protective Feet** **Fig.103**  
Adhere custom-made 3M™ Bumpon™ MB1102-113 to specialty desk-top items such as trophies to act as a cushion and to protect surfaces from scratching.



**Customized Clear Cushioners** **Fig.104**  
Designed with clear and white laptop computers in mind, 3M™ Bumpon™ MB1202-102 clear cushioners discreetly prevent slippage and protect surfaces.



**Customized Non-skid Feet** **Fig.105**  
3M™ Bumpon™ MB1104-105 is ideal for use as non-skid feet on video projectors.

| Product                               | Color              | Adhesive <sup>1</sup> | Shape                              | Width<br>in. (mm)           | Height<br>in. (mm) | Pad<br>Format | Hardness<br>(Shore A) | Comments                           |
|---------------------------------------|--------------------|-----------------------|------------------------------------|-----------------------------|--------------------|---------------|-----------------------|------------------------------------|
| <b>CUSTOMIZED SHAPES* (Continued)</b> |                    |                       |                                    |                             |                    |               |                       |                                    |
| MB1104-109                            | Black              | R-30                  | Elliptical                         | 0.238 (6.0)                 | 0.111 (2.8)        | 8x5           | 70                    | Unique foot shape.                 |
| MB1104-110                            | Black              | R-30                  | Square                             | 0.80 (20.3)                 | 0.10 (2.5)         | 5x3           | 70                    | Good load bearer.                  |
| MB1104-132                            | Black              | R-30                  | Cone                               | 0.787 (20.0)                | 0.591 (15.0)       | 4x4           | 70                    | Small contact point.               |
| MB1202-102                            | Transparent        | A-20                  | Oval                               | 0.298 (7.6)                 | 0.118 (3.0)        | 1x9           | 70                    | Unique clear shape.                |
| MB1202-111                            | Transparent        | A-20                  | Rectangular                        | 0.197 x 0.315 (5.0 x 8.0)   | 0.063 (1.6)        | 10x7          | 75                    | Unique clear shape.                |
| MB1202-132                            | Transparent        | A-20                  | Cone                               | 0.787 (20.0)                | 0.591 (15.0)       | 4x4           | 75                    | Small contact point.               |
| SJ5321                                | Transparent        | A-20                  | Cylindrical with Recess            | 1.299 (33.0)                | 0.314 (8.0)        | 3x6           | 75                    | Universal color matching.          |
| SJ5346                                | Transparent        | A-20                  | Tapered Square                     | 0.906 (23.0)                | 0.235 (6.0)        | 4x4           | 75                    | Universal color matching.          |
| SJ5349                                | Transparent        | A-20                  | Rectangular                        | 0.625 x 1.5 (15.9 x 38.1)   | 0.4 (10.2)         | 6x2           | 75                    | Universal color matching.          |
| SJ5363                                | Transparent        | A-20                  | Cylindrical/Hemispherical Top      | 0.858 (21.8)                | 0.224 (5.7)        | 4x8           | 75                    | Universal color matching.          |
| SJ5369                                | Transparent        | A-20                  | Rectangular                        | 0.213 x 0.65 (5.4 x 16.5)   | 0.062 (1.6)        | 6x12          | 75                    | Universal color matching.          |
| SJ5378                                | Transparent        | A-20                  | Hemispherical with Flat Top        | 0.4 (10.2)                  | 0.13 (3.3)         | 7x8           | 75                    | Unique clear shape.                |
| SJ5384                                | Transparent        | A-20                  | Rectangular                        | 0.213 x 0.65 (5.4 x 16.5)   | 0.123 (3.1)        | 6x12          | 75                    | Universal color matching.          |
| SJ5386                                | Transparent        | A-20                  | Cylindrical with Concavity         | 1.24 (31.5)                 | 0.238 (6.0)        | 3x6           | 75                    | Universal color matching.          |
| SJ5389                                | Transparent        | A-20                  | Square                             | 0.786 (20.0)                | 0.255 (6.5)        | 4x9           | 75                    | Universal color matching.          |
| SJ5386                                | Clear              | A-20                  | Square Base with Cylindrical Top   | 0.812 (20.6)                | 0.62 (15.7)        | 4x3           | 75                    | Unique load bearing shape.         |
| SJ5711                                | Black              | R-30                  | Rectangular                        | 0.245 x 0.96 (6.2 x 24.4)   | 0.10 (2.5)         | 4x10          | 70                    | Unique narrow shape.               |
| SJ5719                                | Black              | R-30                  | Rectangular                        | 0.397 x 0.795 (10.1 x 20.2) | 0.302 (7.7)        | 5x10          | 70                    | Unique shape.                      |
| SJ5721                                | Gray               | R-30                  | Cylindrical with Recess            | 1.299 (33.0)                | 0.314 (8.0)        | 3x6           | 70                    | Good load, tapered bearing design. |
| SJ5726                                | Black              | R-30                  | Oval                               | 0.266 (6.8)                 | 0.059 (1.5)        | 4x20          | 70                    | Low profile shape.                 |
| SJ5737                                | Black              | R-30                  | Rectangular                        | 0.236 x 0.59 (6.0 x 15.0)   | 0.138 (3.5)        | 6x18          | 70                    | Unique narrow shape.               |
| SJ5739                                | Black              | R-30                  | Rectangular                        | 0.350 x 0.73 (8.9 x 18.5)   | 0.31 (7.9)         | 5x8           | 70                    | High profile shape.                |
| SJ5742                                | Black              | R-30                  | Rectangular                        | 0.354 x 0.728 (9.0 x 18.5)  | 0.18 (4.6)         | 5x9           | 70                    | Medium profile — general use.      |
| SJ5743                                | Black, White       | R-30                  | Rectangular                        | 0.312 x 1.0 (7.9 x 25.4)    | 0.062 (1.6)        | 4x12          | 70                    | Special grooved design.            |
| SJ5746                                | Black, White, Gray | R-30                  | Tapered Square                     | 0.906 (23.0)                | 0.235 (6.0)        | 4x4           | 70                    | Good load bearing capacity.        |
| SJ5749                                | Black              | R-30                  | Rectangular                        | 0.625 x 1.5 (15.9 x 38.1)   | 0.40 (10.2)        | 6x2           | 70                    | Unique angled shape.               |
| SJ5751                                | Black, White       | R-30                  | Rectangular                        | 0.531 x 0.984 (13.5 x 25.0) | 0.067 (1.7)        | 4x6           | 70                    | Low profile.                       |
| SJ5755                                | Black              | R-30                  | Oval                               | 0.213 x 0.764 (5.4 x 19.4)  | 0.125 (3.2)        | 4x18          | 70                    | Unique flat top oval.              |
| SJ5759P                               | Black              | R-30                  | "L" Shaped                         | 1.063 (27.0)                | 0.125 (3.2)        | 4x2           | 70                    | Unique L shape.                    |
| SJ5762                                | Black              | R-30                  | Rectangular with Rounded Ends      | 0.5 x 0.94 (12.7 x 23.9)    | 0.13 (3.3)         | 4x4           | 70                    | Unique curved top.                 |
| SJ5763                                | Gray               | R-30                  | Cylindrical with Hemispherical Top | 0.858 (21.8)                | 0.224 (5.7)        | 4x8           | 70                    | Unique hemispheric top shape.      |
| SJ5765                                | Black              | R-30                  | Square                             | 0.437 (11.1)                | 0.23 (5.8)         | 9x6           | 70                    | Unique load bearing shape.         |
| SJ5775                                | Black              | R-30                  | Square                             | 1.391 (35.3)                | 0.874 (22.2)       | indiv. pcs.   | 70                    | Large load bearing shape.          |
| SJ5778                                | White              | R-30                  | Hemispherical with Flat Top        | 0.4 (10.2)                  | 0.13 (3.3)         | 7x8           | 70                    | Good energy absorption on impact.  |
| SJ5779                                | Black              | R-30                  | Rectangular                        | 0.52 x 0.77 (13.2 x 19.6)   | 0.18 (4.6)         | 5x5           | 70                    | Good load bearing.                 |
| SJ5781                                | Black              | R-30                  | Elliptical                         | 0.359 (9.1)                 | 0.155 (3.9)        | 4x9           | 70                    | Unique elliptical shape.           |
| SJ5786                                | Gray               | R-30                  | Cylindrical with Concavity         | 1.24 (31.5)                 | 0.238 (6.0)        | 3x6           | 70                    | Recessed center design.            |
| SJ5787                                | Sunlight Purple    | R-30                  | Rectangular with Rounded Ends      | 0.243 x 1.037 (6.2 x 26.3)  | 0.155 (3.9)        | 3x10          | 70                    | Dome foot design.                  |
| SJ5789                                | Black              | R-30                  | Square                             | 0.786 (20.0)                | 0.255 (6.5)        | 4x9           | 70                    | Good load bearing.                 |
| SJ5796                                | Black              | R-30                  | Cylindrical with Hemispherical Top | 0.363 (9.2)                 | 0.199 (5.1)        | 7x8           | 70                    | Unique curved top.                 |
| SJ5797                                | White              | R-30                  | Rectangular with Rounded Ends      | 0.477 x 0.675 (12.1 x 17.1) | 0.139 (3.5)        | 8x4           | 70                    | General purpose foot.              |
| SJ5799                                | Black              | R-30                  | Rectangular                        | 0.339 x 0.476 (8.6 x 12.1)  | 0.142 (3.6)        | 8x7           | 70                    | General use.                       |
| SJ57B2                                | Black              | R-30                  | Square with Rounded Corners        | 0.50 (12.7)                 | 0.213 (5.4)        | 7x4           | 70                    | Good load bearing shape.           |
| SJ57B3                                | Black              | R-30                  | Square with Rounded Corners        | 0.50 (12.7)                 | 0.134 (3.4)        | 7x4           | 70                    | Good load bearing shape.           |
| SJ57B4                                | Black              | R-30                  | Rectangular with One Rounded End   | 0.336 x 0.405 (8.5 x 10.3)  | 0.102 (2.6)        | 7x8           | 70                    | Unique foot design shape.          |
| SJ57B6                                | Black, White       | R-30                  | Square Base with Cylindrical Top   | 0.812 (20.6)                | 0.62 (15.7)        | 4x3           | 70                    | Excellent load bearing.            |
| SJ6122                                | Black              | R-25                  | Tapered Square                     | 0.410 (10.4)                | 0.125 (3.2)        | 9x5           | 70                    | Quick stick.                       |

<sup>1</sup> **A-20: Acrylic** — high strength adhesion to high energy surface. **R-25: Synthetic Rubber** — ideal for low surface energy substrates.

**R-30: Natural Rubber** — excellent adhesion to a wide variety of surfaces.

\*Made to order products. Available with 10-day lead time. Minimum order 30,000 pieces.

Note: This technical information and data should be considered representative or typical only and should not be used for specification purposes.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## 3M:

[SJ3542V](#) [SJ-3527 \(WHITE\) 5/8"](#) [SJ-3530 \(BLACK\) 2"](#) [SJ3526-BLACK-2"](#) [SJ3542 \(Black\) 1" x 50 yd](#) [SJ-3526\(WHITE\)2"](#) [SJ3527N 5/8 X 50YD BLACK](#) [SJ-3526N-HOOK-WHITE-1"](#) [SJ-3527N-WHITE \(1X50YD\)](#) [SJ3523 1" BLK \(50 YD ROLL\)](#) [SJ-4570 1" CLEAR](#) [SJ-3531\(BLACK\) 2"](#) [SJ-3402-2" WHITE](#) [SJ-3527 \(BLACK\) 2"](#) [SJ-3402-1" WHITE](#) [SJ-3527 \(WHITE\) 2"](#) [SJ-3551 2" BLK](#) [SJ3522](#) [SJ3523](#) [SJ3531](#) [SJ3551](#) [SJ3571](#) [SJ61A11](#) [SJ61A3](#) [SJ3526N WHITE 5/8" X 50YD](#) [SJ3526N WHITE 1/2X50YD](#) [SJ3526N BEIGE 3/4" X 50YD](#) [SJ3526N SILVER 1 1/2" X 50YD](#) [SJ3526N WHITE 2"X100YD](#) [SJ3526N BEIGE 4"X50YD](#) [SJ3526N BEIGE 2"X100YD](#) [SJ3526N BLACK 1"X100YD](#) [SJ3526N BEIGE 5/8" X 50YD](#) [SJ3526N WHITE 3/4" X 50YD](#) [SJ3526N BLACK 1 1/2" X 50YD](#) [SJ3526N SLATE GRAY 1"X50YD](#) [SJ3526N BLACK 3/4" X 50YD](#) [SJ3526N BEIGE 1 1/2"X50YD](#) [SJ3526N LT GRAY 1"X50YD](#) [SJ3526N WHITE 4"X50YD](#) [SJ3526N WHITE 1"X 25YD](#) [SJ3526N BLACK 5/8" X 50YD](#) [SJ3526N SLATE GRAY 2"X50YD](#) [SJ3526N BEIGE 1" X 50YD](#) [SJ3526N BLACK 4"X50YD](#) [SJ3526N WHITE 1"X100YD](#) [SJ3526N BLACK 1"X 25YD](#) [SJ3526N BLACK 1/2" X 50YD](#) [SJ3526N BLACK 2"X100YD](#) [SJ3526N BEIGE 1"X100YD](#) [SJ3572-5/8](#) [SJ3401-1"x50yd-White](#) [SJ3402-3/4"x50yd-Black](#) [SJ3526N-Beige-2"x50yd](#) [SJ3527N-Beige-1"x50yd](#) [SJ3527N-Beige-2"x50yd](#) [SJ3527N-Beige-5/8"x50yd](#) [SJ3527N-Black-1.5"x50yd](#) [SJ3571-White-2"x50yd](#) [SJ4570-3/4"x50yd-Clear](#) [SJ4570-4"x50yd-Clear](#) [SJ4570-4"x75yd-Clear](#) [SJ3401-2"x50yd](#) [SJ3402-2"x50yd](#) [SJ-3532N-Hook-Black-1"](#) [SJ-3533N-Loop-Black-1"](#) [SJ3550-2"X50YD-BLACK](#) [SJ3552-1"x50yd](#) [SJ-3571-1"x50yd-Black](#) [SJ3571-1"x50yd-White](#) [SJ3571-5/8"x50yd-Black](#) [SJ3572-2"x50yd-Black](#) [SJ4570-5/8"x50yd-Clear](#) [SJ3401-11/2x50](#) [SJ3401-5/8x50](#) [SJ3402-11/2x50](#) [SJ3402-5/8x50](#) [SJ3418FR-2x50](#) [SJ3418FR-5/8x50](#) [SJ3419FR-2x50](#) [SJ3419FR-5/8x50](#) [SJ3518FR-1x50](#) [SJ3518FR-5/8x50](#) [SJ3530-1x50](#) [SJ3530-2x50](#) [SJ3530-3/4x50](#) [SJ3531-1x50](#) [SJ3531-2x50](#) [SJ3532N-11/2x50](#) [SJ3532N-5/8x50](#) [SJ3533N-1x50](#) [SJ3533N-2x50](#) [SJ3542-1/2x50](#) [SJ3542-2x50](#) [SJ3552-1/2x50](#) [SJ3552-2x50](#) [SJ3560-1/2x50](#) [SJ3560-2x50](#) [SJ5474](#) [SJ57B1-3000BLK](#)