

[support](#) | [locate distributor](#) | [about panduit](#) | [contact us](#)*World Leader in Network and Electrical Solutions*[HOME](#) | [SOLUTIONS](#) | [RESOURCES](#) | [PRODUCTS](#) | [SERVICES](#) | [LEARNING](#)

SEARCH

Current refinements (click ☒ to remove)☒ **Region** ▶ **USA** ☒ **Product Family** ▶ **HSTTV Heat Shrink on Bulk Reels** ☒ **Text Search:** 'HSTTV75-T'**Your search criteria matched only one product, shown below.****Flexible Polyolefin VW-1 DRY-SHRINK™ Heat Shrink Tubing in Bulk Reels**

- For dry locations
- Highly flame retardant Meets UL VW-1 Rating
- Fast Shrink Time
- Material Type: Highly Flexible Crosslinked Polyolefin
- Shrink Ratio: 2:1
- Temperature Range: -67°F to 257°F (-55°C to 125°C)
- Voltage: 600V
- UL VW-1 Recognized, CSA Certified
- Mil Spec: AMS-DTL-23053/5 Class 3

Part Number:	HSTTV75-T
RoHS Compliancy Status:	Compliant
Part Description:	Thin Wall Polyolefin Heat Shrink (UL224 VW-1)
Material:	Polyolefin cross-linked
Color:	Black
CSA Certified:	Yes
Military Specification:	AMS-DTL-23053/5 Class 3
UL Recognized:	E122770
Length (ft.):	200
Length (m):	61.0
Flammability Rating:	UL224 VW-1
Max. Recovered I.D. (In.):	.375
Max. Recovered I.D. (mm):	9.5
Min. Expanded I.D. (In.):	.750
Min. Expanded I.D. (mm):	19.0
Nominal Diameter / Size:	3/4
Nominal Recovered Wall Thickness (In.):	.03
Nominal Recovered Wall Thickness (mm):	.8
Shrink Ratio:	2:1
Temperature Range:	-67°F to 257°F (-55°C to 125°C)
Min. Order UOM:	RL
Min. Order Qty.:	1
BOM Qty. (# of Pkgs.)	0
Add to My Catalog	☐

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'My Catalog' features.

[legal information](#) | [privacy policy](#) | [site map](#)

Copyright © 1995-2007, PANDUIT CORP. All rights reserved.